


EcoBand Panel – Cat5E UTP



- Vertical IDC punch down
- Integral Rear Cable Management
- 25 Year System Warranty

Product Description

The Cat5E EcoBand Panel presents 24 Cat5E RJ45 ports in 1U of space with vertical IDC punch down for ease of termination. The robust body of the panel provides integrated rear cable management with a range of cable fixing locations.

Each individual port is screen printed for easy identification with space for end user labelling.

Each panel comes supplied with Rack Snap as standard.

Features and Benefits

- Vertical IDC punch down presentation
- Cost effective solution
- Exceeds all ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2 Cat5E performance standards
- Manufactured to exacting ISO 9001 quality standards
- Built in rear cable management
- High density 24 ports in 1U
- Write on label strip
- Accepts Krone style punch down tools
- 568A or 568B wiring options
- RoHS compliant - lead free
- Backward compatible with Cat5 and voice

Product Description	Ordering Code	UNS Number
EcoBand Panel – Cat5E UTP	HT2408PBU5E-M/BK	853-35056

Technical Description

The Cat5E EcoBand Panel presents 24 Cat5E RJ45 ports in 1U of space and comes with cable management as standard with each individual port being screen printed for easy identification.

Tested to exceed all ISO/IEC 11801 and ANSI/TIA/EIA 568-C.2 Cat5E performance standards.

Dimensions and Product Construction Specification


Ordering Code	Height	Width	Depth	Weight (Approx)
HT2408PBU5E-M/BK	44.00mm	482.50mm	132.00mm	1.62kg

- Jack life min. 1000 insertions
- Wire gauge 22-26 AWG
- Insertion loss <0.1dB 1-100MHz worst pair
- Maximum thickness of wire and insulation 1.44mm dia.
- Max. of two wires per contact (same gauge)
- IDC life up to 50 re-terminations

Applications Supported

The Cat5E EcoBand panel is designed to support any data or voice protocol that is capable offering over a Cat5E cabling system and is backward compatible with existing Cat5 and voice network infrastructure.

Technical Drawings



Tel: +44 (0) 1604 707420

Web: www.htdata.co.uk

Email: sales@htdata.co.uk