

DURACELL®



ULTRA POWER

MX1400


Size: C (LR14)

Alkaline-Manganese Dioxide Battery

Zn/MnO₂




Nominal voltage	1.5 V
Impedance	130 m-ohm @ 1 kHz
Typical weight	71 g (2.4 oz)
Typical volume	26.9 cm ³ (1.6 in ³)
Terminals	Flat
Storage temperature range	5°C to 30°C (41°F to 86°F)
Operating temperature range	-20°C to 54°C (-4°F to 130°F)
Designation	IEC: LR14




Dimensions shown are IEC standards

Ultra Power C Constant Current



Ultra Power C Constant Current



DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.

DURACELL®



ULTRA POWER


MX1400

Size: C (LR14)


Alkaline-Manganese Dioxide Battery

Zn/MnO₂


Ultra Power C Constant Power



Ultra Power C Constant Resistance



Ultra Power C Constant Temperature at 250 mA



DURACELL®

BATTERIES

Berkshire Corporate Park
Bethel, CT. 06801 U.S.A.
Telephone: Toll-free 1-800-544-5454
www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.