


CMX1211X132B-10

PHYSICAL DIMENSIONS:

A	31.50	MAX
B	28.00	MAX
C	19.00	MAX.
D	25.00	REF
E	6.00	± 0.25
F	3.35	± 0.25
G	15.24	± 0.30
H	24.20	± 0.30



ELECTRICAL SPECIFICATION


ELECTRICAL CHARACTERISTICS		NOM	MIN	MAX
INDUCTANCE @ 100KHz/100mV 1-4/2-3	uH	1300	780	1755
DCR 1-4/2-3	mΩ	---	---	10
RATING CURRENT	A	---	---	11
RATING VOLTAGE	Vrms	---	---	250

HIPOT COIL-COIL: 1500VAC


NOTES: UNLESS OTHERWISE SPECIFIED

- COMPONENTS SHOULD BE ADEQUATELY PREHEATED BEFORE SOLDERING.
- TIN: LEAD-FREE SOLDER BAR.
- BASE MATERIAL: PHENOLIC RESIN.
- THIS PART HAS NO PIN POLARITY.
- OPERATION TEMPERATURE RANGE:
-40°C TO +125°C (INCLUDING SELF-HEATING).



EQUIVALENT CIRCUIT



LAND PATTERNS FOR REFLOW SOLDERING



RECOMMENDED SOLDERING CONDITIONS



UNCONTROLLED DOCUMENT

AGILENT E4991A RF Impedance/Material Analyzer
HP 16092A Test Fixture.

DIMENSIONS ARE IN mm .				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
				PROJECT/PART NUMBER:	REV	PART TYPE:	DRAWN BY:
C	CHANGE RATING VOLTAGE UNIT	03/11/13	QIU	CMX1211X132B-10	C	CMX	QIU
B	ADD BOTTOM VIEW AND NOTE 3	01/03/13	QIU	DATE:	11/14/12	SCALE:	NTS
A	ORIGINAL DRAFT	11/14/12	QIU	CAD #		TOOL #	
REV	DESCRIPTION	DATE	INT	CMX1211X132B-10-C			1 of 1

