


REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
C	PRODUCT DRAWING (EAR 13398)	OCT31/08	K.L.

MOUNTING CODE 4
4-40 UNC THREAD
OR
MOUNTING CODE 6
M3 x 0.5 THREAD
X .240 [6.10] MIN.
DEEP (4 PLACES)



ORDERING CODE: F C E 1 7 - B 2 5 A D - 4 0 0 G

SERIES
FCE17=FILTERED D-SUB, RoHS

SIZE/NUMBER OF CONTACTS
E09, A15, B25, OR C37

CONNECTOR STYLE
AD=PIN/SOCKET ADAPTER



MOUNTING
2=.120 [3.05] DIA. THROUGH HOLE
WITH #4-40 MOUNTING POST
4=#4-40 UNC THREAD
6=M3 x 0.5 THREAD
K=.120 [3.05] DIA. THROUGH HOLE
WITH M3 x 0.5 MOUNTING POST

CONTACT FINISH/GOLD THICKNESS
NO DIGIT=STANDARD 15 MICROINCHES
[0.38 MICRONS] GOLD ON
MATING AREA
G=50 MICROINCHES [1.27 MICRONS]
GOLD ON MATING AREA

MODIFIER
O=STANDARD

FILTER CAPACITANCE
D=50 pF 5=1000 pF
B=100 pF 7=1200 pF
O=180 pF 6=1300 pF
T=220 pF J=1500 pF
F=330 pF E=2200 pF
L=380 pF 9=5600 pF
1=470 pF 8=47000 pF
2=680 pF N=NO FILTERS
4=820 pF

REFER TO AMPHENOL CATALOGUE
FOR FILTER PERFORMANCE
CHARACTERISTICS




NOTES:


- MATERIALS: — ALL MATERIALS ARE RoHS COMPLIANT
— SHELLS: TIN PLATED STEEL
— CONTACTS: PHOSPHOR BRONZE
PLATED WITH GOLD OVER 50µ" [1.27 MICRONS]
NICKEL ON MATING AREA. SEE ORDERING CODE.
— INSULATOR: ENGINEERING THERMOPLASTIC, GLASS
REINFORCED, FLAMMABILITY RATING UL94V-0, BLACK.
— OUTSIDE SHELLS: ZINC DIECAST, NICKEL PLATED
— MOUNTING HARDWARE: STEEL OR COPPER ALLOY,
TIN OR NICKEL PLATED
- CONTACT RESISTANCE: 30 MILLIOHMS MAXIMUM
- INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
- CURRENT RATING: 5 AMPS MAXIMUM
- OPERATING TEMPERATURE: -40°C TO 85°C.
- TOLERANCE, UNLESS INDICATED OTHERWISE, ±.005 [0.13].

SIZE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]
E09	1.213 [30.81]	.643 [16.33]	.666 [16.92]	.984 [24.99]
A15	1.541 [39.14]	.971 [24.66]	.994 [25.25]	1.312 [33.32]
B25	2.088 [53.04]	1.511 [38.38]	1.534 [38.96]	1.852 [47.04]
C37	2.729 [69.32]	2.159 [54.84]	2.182 [55.42]	2.500 [63.50]

MOUNTING CODES 2 & K
.120 [3.05] DIA THROUGH
HOLE (2 PLACES) AND
MOUNTING POST (2 SUPPLIED
LOOSE PER CONNECTOR)



CAPACITANCE SCHEMATIC
FOR EACH POSITION



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.



DRAWN S.BUENAVIDES	DATE DEC08/05	Amphenol Canada Corp.	
DESIGNED			
CHECKED K.LAMBIE	DEC08/05		
I. E. APPRD.			
Q. A. APPRD.		FCE17 SERIES FILTERED D-SUB CONNECTOR, MALE/FEMALE ADAPTER, RoHS COMPLIANT	
DWG. APPRD.			
ENG. REL. NO.		DWG	DRAWING NO.
REF. EAR 12888		C	P-FCE17-XXXAD-XX0X
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554	SCALE 2/1	WT. -----
		SURF. -----	SHEET 1 of 1