


Product data sheet

Characteristics

GVAN113

TeSys GV2 & GV3 - auxiliary contact block - 1 NO + 1 NC

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Commercial Status	Commercialised
Range of product	TeSys GV2 TeSys GV3
Device short name	GVAN
Product or component type	Auxiliary contact block
Product compatibility	GV2L GV2LE GV2ME GV2P GV2RT GV3L GV3P
Pole contact composition	1 NO + 1 NC
Connections - terminals	Control circuit: spring terminals 2 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Control circuit: spring terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end

Complementary

Mounting location	Left side
[Ui] rated insulation voltage	600 V - conforming to CSA C22.2 No 14 690 V - conforming to IEC 60947-1 600 V - conforming to UL 508
[Ue] rated operational voltage	24...240 V DC 48...690 V AC
[Ith] conventional free air thermal current	6 A
Protection type	GG fuse <= 10 A GB2CB... circuit breaker rating according to operational current for Ue <= 415 V
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 400 VA at 690 V AC-15 - electrical durability: 100000 cycles 300 VA at 48 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	240 W at 48 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 120 W at 240 V DC-13 - electrical durability: 100000 cycles
Height	3.5 in (89 mm)
Width	0.37 in (9.3 mm)
Depth	2.6 in (66 mm)
Product weight	0.13 lb(US) (0.06 kg)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901494911
Nbr. of units in pkg.	1
Package weight(Lbs)	0.50
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	N
Country of origin	CZ

Contractual warranty

Period	18 months
--------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAN113](#)