


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E4	REVISED PER ECO-13-005565	02APR13	KH	JO

- | | |
|---|--|
| 1 | HOUSING: GLASS FILLED POLYESTER, PCT, COLOR: BLACK |
| 2 | CONTACT: PHOSPHOR BRONZE |
| 3 | CONTACT: DUPLEX PLATING 0.00076[.000030] GOLD IN CONTACT AREA, 0.00381-0.00762[.000150-.000300] TIN-LEAD ON SOLDER LEADS ALL OVER 0.00127-0.00254[.000050-.000100] NICKEL. |
| 4 | MOLDED IN ARROW DESIGNATES MATING FACE OF CONNECTOR. |
| 5 | DIMENSIONS PERTAINS TO CAVITY CENTERLINES. |
| 6 | DATUMS AND BASIC DIMENSIONS ARE ESTABLISHED BY THE CUSTOMER. |
| 7 | OBSOLETE PART |
| 8 | NO PART NUMBER MARKING REQUIRED FOR THIS PART. |


- | | | | |
|----|---|----|---------|
| 9 | TE LOGO AND CSA LOGO ARE MOLDED INTO HOUSING, THIS LOCATION. | E4 | REVISED |
| 10 | MARK PART NUMBER AND DATE CODE IN APPROXIMATE LOCATION SHOWN, EITHER END. | | |
| 11 | SUPERSEDED BY 5147721-2 | | |



RECOMMENDED PC BOARD LAYOUT

7	165.10	[6.500]	65	6-147721-4
7	162.56	[6.400]	64	6-147721-3
7	160.02	[6.300]	63	6-147721-2
7	157.48	[6.200]	62	6-147721-1
7	152.94	[6.100]	61	6-147721-0
7	152.40	[6.000]	60	5-147721-9
7	149.86	[5.900]	59	5-147721-8
7	147.32	[5.800]	58	5-147721-7
7	144.78	[5.700]	57	5-147721-6
7	142.24	[5.600]	56	5-147721-5
7	139.70	[5.500]	55	5-147721-4
7	137.16	[5.400]	54	5-147721-3
7	134.62	[5.300]	53	5-147721-2
7	132.08	[5.200]	52	5-147721-1
7	129.54	[5.100]	51	5-147721-0
7	127.00	[5.000]	50	4-147721-9
7	124.46	[4.900]	49	4-147721-8
7	121.92	[4.800]	48	4-147721-7
7	119.38	[4.700]	47	4-147721-6
7	116.84	[4.600]	46	4-147721-5
7	114.30	[4.500]	45	4-147721-4
7	111.76	[4.400]	44	4-147721-3
7	109.22	[4.300]	43	4-147721-2
7	106.68	[4.200]	42	4-147721-1
7	104.14	[4.100]	41	4-147721-0

	101.60[4.000]	40	3-147721-9
	99.06[3.900]	39	3-147721-8
	96.52[3.800]	38	3-147721-7
	93.98[3.700]	37	3-147721-6
	91.44[3.600]	36	3-147721-5
	88.90[3.500]	35	3-147721-4
	86.36[3.400]	34	3-147721-3
	83.82[3.300]	33	3-147721-2
	81.28[3.200]	32	3-147721-1
	78.74[3.100]	31	3-147721-0
	76.20[3.000]	30	2-147721-9
	73.66[2.900]	29	2-147721-8
	71.12[2.800]	28	2-147721-7
	68.58[2.700]	27	2-147721-6
	66.04[2.600]	26	2-147721-5
	63.50[2.500]	25	2-147721-4
	60.96[2.400]	24	2-147721-3
	58.42[2.300]	23	2-147721-2
	55.88[2.200]	22	2-147721-1
	53.34[2.100]	21	2-147721-0
	50.80[2.000]	20	1-147721-9
	48.26[1.900]	19	1-147721-8
	45.72[1.800]	18	1-147721-7
	43.18[1.700]	17	1-147721-6
	40.64[1.600]	16	1-147721-5
	38.10[1.500]	15	1-147721-4
	35.56[1.400]	14	1-147721-3
	33.02[1.300]	13	1-147721-2
	30.48[1.200]	12	1-147721-1
	27.94[1.100]	11	1-147721-0
	25.40[1.000]	10	147721-9
	22.86[.900]	9	147721-8
	20.32[.800]	8	147721-7
	17.78[.700]	7	147721-6
	15.24[.600]	6	147721-5
△8	12.70[.500]	5	147721-4
△8	10.16[.400]	4	147721-3
△11△8	7.62[.300]	3	147721-2
△8	5.08[.200]	2	147721-1

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.BINNER		25OCT01		 TE Connectivity						
			CHK —		—								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME		AMPMODU MODII RECPT. ASSY., HORZ., SURFACE MOUNT, .100CL, 1 ROW CLOSED ENTRY, END STACK					
		0 PLC ± —		PRODUCT SPEC —									
		1 PLC ± —		—									
		2 PLC ± —		APPLICATION SPEC —									
3 PLC ± .005		4 PLC ± —		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT —		A2		00779	 147721	—			
				CUSTOMER DRAWING									
							SCALE		5:1	SHEET	1 OF 1	REV	F4