


LOC		DIST		REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVO	
			D	REVISE PER 06-??????????	04/APR/06	ECC	FDM	



PRODUCT CODE
P — FLEXPAC CABLE
S — FLEXSTRIP

08

P

3

ASSEMBLY LENGTH TO NEAREST TENTH OF AN INCH. SEE CABLE SPECIFICATION DRAWINGS FOR SPECIFIC MEASUREMENT CRITERIA.

F2

—

F3

TOTAL NUMBER OF CONDUCTORS

LEFT END TERMINATION

RIGHT END TERMINATION

P — FLEXPAC CABLE

INSULATION MATERIAL
P — POLYESTER CABLE

S — FLEXSTRIP

N — NOMEX*
T — TEFLON*
K — KAPTON*
P — POLYESTER*

*AVAILABLE ONLY WITH FLEXSTRIP JUMPER.
NOMEX,TEFLON,AND KAPTON ARE TRADEMARKS OF DuPONT.

TERMINATION STYLE

- A STRAIGHT FLEXSTRIP PIN
- B RIGHT ANGLE FLEX STRIP PIN
- C RIGHT ANGLE STAGGERED FLEXSTRIP PIN
- D STRAIGHT STAGGERED FLEXSTRIP PIN
- E FLEXPAC SOLDER PIN STRAIGHT
- E2 FLEXPAC SOLDER PIN RIGHT ANGLE UP
- E3 FLEX PAC SOLDER PIN RIGHT ANGLE DOWN
- F SINGLE ROW SOCKET TIN PLATED
- F1 SINGLE ROW SOCKET POLARIZED UP TIN PLATED
- F2 SINGLE ROW RIGHT ANGLE SOCKET UP TIN PLATED
- F3 SINGLE ROW RIGHT ANGLE SOCKET DOWN TIN PLATED
- F4 SINGLE ROW RIGHT ANGLE SOCKET POLARIZED UP TIN PLATED
- F5 SINGLE ROW RIGHT ANGLE SOCKET POLARIZED DOWN TIN PLATED
- F6 SINGLE ROW SOCKET POLARIZED DOWN TIN PLATED
- G DOUBLE ROW SOCKET TIN PLATED
- G1 DOUBLE ROW SOCKET POLARIZED UP TIN PLATED
- G2 DOUBLE ROW SOCKET POLARIZED DOWN TIN PLATED
- H SINGLE ROW SOCKET GOLD PLATED
- H1 SINGLE ROW SOCKET POLARIZED UP GOLD PLATED
- H2 SINGLE ROW RIGHT ANGLE SOCKET UP GOLD PLATED
- H3 SINGLE ROW RIGHT ANGLE SOCKET DOWN GOLD PLATED
- H4 SINGLE ROW RIGHT ANGLE SOCKET POLARIZED UP GOLD PLATED
- H5 SINGLE ROW RIGHT ANGLE SOCKET POLARIZED DOWN GOLD PLATED
- H6 SINGLE ROW SOCKET POLARIZED DOWN GOLD PLATED
- I DOUBLE ROW SOCKET GOLD PLATED
- I2 DOUBLE ROW SOCKET POLARIZED UP GOLD PLATED
- I3 DOUBLE ROW SOCKET POLARIZED DOWN GOLD PLATED
- J SINGLE ROW MALE TIN PLATED
- L SINGLE ROW MALE GOLD PLATED

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 18/JAN/02	tyco Tyco Electronics Corporation	
DIMENSIONS: INCHES		CHK F.MCCORKEL 05/JUN/02	Harrisburg, PA 17105-3608	
		APVD F.D. McCORKEL 12/MAR/03	NAME FLEXPAC, GENERIC DRAWING	
		PRODUCT SPEC	—	
MATERIAL —		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779
FINISH —		WEIGHT —	DRAWING NO C=1474505	RESTRICTED TO —
CUSTOMER DRAWING			SCALE N.T.S.	SHEET 1 of 7
			REV D	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		—	SEE SHEET 1	—	—	—

D

C

B


A



FLEXPAC CABLE SPECIFICATIONS
CONDUCTOR SIZE [ROLLED OFC]: .076mm[.003]X 1.57mm[.062]
PITCH: 2.54mm [.100]
MATERIAL: BARE COPPER PER QQ-C-502
CABLE DIMENSIONS: .356mm[.014] THICK [NOMINAL]
INSULATION: POLYESTER
UL STYLE NUMBER: 2639
VOLTAGE RATING: 300 VOLT
TEMPERATURE RATING: 105°C
CURRENT RATING: 3 AMPS
CAPACITANCE: 12.6 Pf/ft
RESISTANCE: 43 OHMS/1000 ft
IMPEDANCE: 110Ω

FLEXPAC SOLDER PIN SPECIFICATIONS
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT PLATING: MATTE TIN
CURRENT RATING: 3 AMPS
CONDUCTOR OR CIRCUIT SIZE: .076mm [.003]/.127mm[.005] THICK
x 1.499mm[.059]/1.65mm [.065] WIDE

NOTE: APPLIES TO FLEXPAC & FLEXSTRIP
ASSEMBLY LENGTH TO BE END OF INSULATION TO END OF INSULATION OR
MATING FACE OF CONNECTOR,
OR MATING FACE TO MATING FACE.




FLEXSTRIP JUMPER SPECIFICATIONS
CONDUCTOR: BARE COPPER,TIN PLATED
VOLTAGE RATING: 300 VAC
TEMPERATURE RATING: 105°C POLYESTER/125°C NOMEX
150°C KAPTON & TEFLON
CURRENT RATING: 3 AMPS
RESISTANCE: 65 OHMS/1000 ft
EQUIVALENT WIRE GAUGE: 24 AWG

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF
TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 18/JAN/02		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608							
		CHK F.MCCORKEL 05/JUN/02									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F.D. McCORKEL 12/MAR/03		NAME					
		0 PLC ± -		PRODUCT SPEC		FLEXPAC, GENERIC DRAWING					
		1 PLC ± -		—		—					
		2 PLC ± -		—		—					
		3 PLC ± -		APPLICATION SPEC							
		4 PLC ± -		—							
		ANGLES ± -									
MATERIAL		FINISH		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
—		—		—		A2	00779	C=1474505	—		
CUSTOMER DRAWING						SCALE	N.T.S.	SHEET	2 of 7	REV	D

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-




POSN	DIMENSIONS			
	"A"		"B"	
2	5.08	[.200]	2.54	[.100]
3	7.62	[.300]	5.08	[.200]
4	10.16	[.400]	7.62	[.300]
5	12.70	[.500]	10.16	[.400]
6	15.24	[.600]	12.70	[.500]
7	17.78	[.700]	15.24	[.600]
8	20.32	[.800]	17.78	[.700]
9	22.86	[.900]	20.32	[.800]
10	25.40	[1.000]	22.86	[.900]
11	27.94	[1.100]	25.40	[1.00]
12	30.48	[1.200]	27.94	[1.100]
13	33.02	[1.300]	30.48	[1.200]
14	35.56	[1.400]	33.02	[1.300]
15	38.10	[1.500]	35.56	[1.400]
16	40.64	[1.600]	38.10	[1.500]
17	43.18	[1.700]	40.64	[1.600]
18	45.72	[1.800]	43.18	[1.700]
19	48.26	[1.900]	45.72	[1.800]
20	50.80	[2.000]	48.26	[1.900]
21	53.34	[2.100]	50.80	[2.000]
22	55.88	[2.200]	53.34	[2.100]
23	58.42	[2.300]	55.88	[2.200]
24	60.96	[2.400]	58.42	[2.300]
25	63.50	[2.500]	60.96	[2.400]
26	66.04	[2.600]	63.50	[2.500]
27	68.58	[2.700]	66.04	[2.600]
28	71.12	[2.800]	68.58	[2.700]
29	73.66	[2.900]	71.12	[2.800]
30	76.20	[3.000]	73.66	[2.900]
31	78.74	[3.100]	76.20	[3.000]
32	81.28	[3.200]	78.34	[3.100]

ASSEMBLY LENGTH TOLERANCE
23" AND BELOW ±.10"
24"–60" ±.25"
OVER 60" ±.50"

FLEXPAC FEMALE SOCKET SPECIFICATIONS
STR., SINGLE ROW, .100" CENTER SPACING

CONTACT MATERIAL	COPPER ALLOY CDA 725
CONTACT (GOLD) PLATING	.000050" THICK GOLD OVER NICKEL IN CONTACT ENGAGEMENT AREA
CONTACT (TIN) PLATING	.000100–.000200 MATTE TIN OVER .000050 MIN. NICKEL
CURRENT RATING	3 AMPS
HOUSING	SINGLE ROW: UP TO 32 CONTACTS GLASS FILLED POLYESTER 94V–0 RATED
POLARIZING PIN	PART NO. 609–0000 INSERTION DEPTH 6.35mm [.250] TO 7.37mm [.290]
INSERTION FORCE	5.14 OZ. PER CONTACT
WITHDRAWAL FORCE	4.30 OZ. PER CONTACT
INSERTION DEPTH	MIN .20 – MAX .35 INCHES



1. ASSEMBLY LENGTH TO BE, END OF INSULATION TO END OF INSULATION OR MATING FACE OF CONNECTOR, OR MATING FACE TO MATING FACE.
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230–702.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

APVD

F.D. McCORKEL

12/MAR/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

DWN

E.C. CLAYBAUGH

18/JAN/02

CHK

F.McCORKEL

05/JUN/02

APVD

F.D. McCORKEL

12/MAR/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105–3608

NAME

FLEXPAC, GENERIC DRAWING

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1474505

RESTRICTED TO

-

SCALE

N.T.S.



SHEET

3 of 7

REV

D

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN APVD
		—		SEE SHEET 1	—	—



POSN	DIMENSIONS	
	"A"	"B"
4	5.08 [.200]	2.54 [.100]
6	7.62 [.300]	5.08 [.200]
8	10.16 [.400]	7.62 [.300]
10	12.70 [.500]	10.16 [.400]
12	15.24 [.600]	12.70 [.500]
14	17.78 [.700]	15.24 [.600]
16	20.32 [.800]	17.78 [.700]
18	22.86 [.900]	20.32 [.800]
20	25.04 [1.000]	22.86 [.900]
22	27.94 [1.100]	25.40 [1.00]
24	30.48 [1.200]	27.94 [1.100]
26	33.02 [1.300]	30.48 [1.200]
28	35.56 [1.400]	33.02 [1.300]
30	38.10 [1.500]	35.56 [1.400]
32	40.64 [1.600]	38.10 [1.500]
34	43.18 [1.700]	40.64 [1.600]
36	45.72 [1.800]	43.18 [1.700]
38	48.26 [1.900]	45.72 [1.800]
40	50.80 [2.000]	48.26 [1.900]
42	53.34 [2.100]	50.80 [2.000]
44	55.88 [2.200]	53.34 [2.100]
46	58.42 [2.300]	55.88 [2.200]
48	60.96 [2.400]	58.42 [2.300]
50	63.50 [2.500]	60.96 [2.400]
52	66.04 [2.600]	63.50 [2.500]
54	68.58 [2.700]	66.04 [2.600]
56	73.66 [2.800]	68.58 [2.700]
58	73.66 [2.900]	71.12 [2.800]
60	76.20 [3.000]	73.66 [2.900]
62	78.74 [3.100]	76.20 [3.000]
64	81.28 [3.200]	78.34 [3.100]

ASSEMBLY LENGTH TOLERANCE
23" AND BELOW ±.10"
24"—60" ±.25"
OVER 60" ±.50"

FLEXPAC FEMALE SOCKET SPECIFICATIONS
STR., 2 ROW, .100" CENTER SPACING

CONTACT MATERIAL	COPPER ALLOY CDA 725
CONTACT (GOLD) PLATING	.000050" THICK GOLD OVER NICKEL IN CONTACT ENGAGEMENT AREA
CONTACT (TIN) PLATING	.000100—.000200 MATTE TIN OVER .000050 MIN. NICKEL
CURRENT RATING	3 AMPS
HOUSING	DOUBLE ROW: UP TO 64 CONTACTS GLASS FILLED POLYESTER 94V-0 RATED
POLARIZING PIN	PART NO. 609-0000 INSERTION DEPTH 6.35mm [.250] TO 7.37mm [.290]
INSERTION FORCE	5.14 OZ. PER CONTACT
WITHDRAWAL FORCE	4.30 OZ. PER CONTACT
INSERTION DEPTH	MIN .20 — MAX .35 INCHES

- ASSEMBLY LENGTH TO BE, END OF INSULATION TO END OF INSULATION OR MATING FACE OF CONNECTOR, OR MATING FACE TO MATING FACE.
- PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	—
1 PLC	±	—
2 PLC	±	—
3 PLC	±	—
4 PLC	±	—
ANGLES	±	—
FINISH	—	—

APVD

F.D. McCORKEL

12/MAR/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

DWN

E.C. CLAYBAUGH

18/JAN/02

CHK

F.MCCORKEL

05/JUN/02

APVD

F.D. McCORKEL

12/MAR/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

tyco Electronics

Tyco Electronics Corporation

Harrisburg, PA 17105-3608

NAME

FLEXPAC, GENERIC DRAWING

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1474505

RESTRICTED TO

—

SCALE

N.T.S.


SHEET

4 of 7

REV

D

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
GP	00		—	SEE SHEET 1	—	—



POSN	DIMENSIONS	
	"A"	"B"
2	9.1 [.390]	2.54 [.100]
3	12.45 [.490]	5.08 [.200]
4	14.99 [.590]	7.62 [3.00]
5	17.53 [.690]	10.16 [.400]
6	20.07 [.790]	12.70 [.500]
7	22.61 [.890]	15.24 [.600]
8	25.15 [.990]	17.78 [.700]
9	27.69 [1.090]	20.32 [.800]
10	30.23 [1.190]	22.86 [.900]
11	32.77 [1.290]	25.40 [1.00]
12	35.31 [1.390]	27.94 [1.100]
13	37.85 [1.490]	30.48 [1.200]
14	40.39 [1.590]	33.02 [1.300]
15	42.91 [1.690]	35.56 [1.400]
16	45.47 [1.790]	38.10 [1.500]
17	48.01 [1.890]	40.64 [1.600]
18	50.55 [1.990]	43.18 [1.700]
19	53.09 [2.090]	45.72 [1.800]
20	55.63 [2.190]	48.26 [1.900]
21	58.17 [2.290]	50.80 [2.000]
22	60.71 [2.390]	53.34 [2.100]
23	63.25 [2.490]	55.88 [2.200]
24	65.79 [2.590]	58.42 [2.300]
25	68.33 [2.690]	60.96 [2.400]
26	70.87 [2.790]	63.50 [2.500]
27	73.41 [2.890]	66.04 [2.600]
28	75.95 [2.990]	68.58 [2.700]
29	78.49 [3.090]	71.12 [2.800]
30	81.03 [3.190]	73.66 [2.900]
31	83.57 [3.290]	76.20 [3.000]
32	86.11 [3.390]	78.34 [3.100]

UNLESS OTHER WISE SPECIFIED, THE RIGHT ANGLE SOCKET FACES DOWN IN AN ASSEMBLY.

ASSEMBLY LENGTH TOLERANCE
23" AND BELOW ±.10"
24"—60" ±.25"
OVER 60" ±.50"

FLEXPAC FEMALE SOCKET SPECIFICATIONS

CONTACT MATERIAL	COPPER ALLOY CDA 725
CONTACT (GOLD) PLATING	.000050" THICK GOLD OVER NICKEL IN CONTACT ENGAGEMENT AREA
CONTACT (TIN) PLATING	.000100—.000200 MATTE TIN OVER .000050 MIN. NICKEL
CURRENT RATING	3 AMPS
HOUSING △ 1	SINGLE ROW: UP TO 32 CONTACTS GLASS FILLED POLYESTER 94V-0 RATED
POLARIZING PIN	PART NO. 609-0000 INSERTION DEPTH 6.35mm [.250] TO 7.37mm [.290]
INSERTION FORCE	5.14 OZ. PER CONTACT
WITHDRAWAL FORCE	4.30 OZ. PER CONTACT
INSERTION DEPTH	MIN .20 — MAX .35 INCHES

△1 REF: 1364838 [NON POLARIZED]
1364839 [COVER]
1364840 [POLARIZED]

2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 18/JAN/02	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK F.MCCORKEL 05/JUN/02				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.D. McCORKEL 12/MAR/03	NAME FLEXPAC, GENERIC DRAWING			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH -	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —	SIZE A2			
MATERIAL —		CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C=1474505	RESTRICTED TO —
		SCALE N.T.S.		SHEET 5 of 7	REV D	


LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
		—	—	SEE SHEET 1	—	—

D

C

B

A



POSN	DIMENSIONS	
	"A"	"B"
2	9.1 [.390]	2.54 [.100]
3	12.45 [.490]	5.08 [.200]
4	14.99 [.590]	7.62 [.300]
5	17.53 [.690]	10.16 [.400]
6	20.07 [.790]	12.70 [.500]
7	22.61 [.890]	15.24 [.600]
8	25.15 [.990]	17.78 [.700]
9	27.69 [1.090]	20.32 [.800]
10	30.23 [1.190]	22.86 [.900]
11	32.77 [1.290]	25.40 [1.00]
12	35.31 [1.390]	27.94 [1.100]
13	37.85 [1.490]	30.48 [1.200]
14	40.39 [1.590]	33.02 [1.300]
15	42.91 [1.690]	35.56 [1.400]
16	45.47 [1.790]	38.10 [1.500]
17	48.01 [1.890]	40.64 [1.600]
18	50.55 [1.990]	43.18 [1.700]
19	53.09 [2.090]	45.72 [1.800]
20	55.63 [2.190]	48.26 [1.900]
21	58.17 [2.290]	50.80 [2.000]
22	60.71 [2.390]	53.34 [2.100]
23	63.25 [2.490]	55.88 [2.200]
24	65.79 [2.590]	58.42 [2.300]
25	68.33 [2.690]	60.96 [2.400]
26	70.87 [2.790]	63.50 [2.500]
27	73.41 [2.890]	66.04 [2.600]
28	75.95 [2.990]	68.58 [2.700]
29	78.49 [3.090]	71.12 [2.800]
30	81.03 [3.190]	73.66 [2.900]
31	83.57 [3.290]	76.20 [3.000]
32	86.11 [3.390]	78.34 [3.100]


ASSEMBLY LENGTH TOLERANCE

23" AND BELOW	±.10"
24"—60"	±.25"
OVER 60"	±.50"

FLEXPAC MALE CONNECTOR SPECIFICATIONS
.100 " CENTER SPACING

CONTACT MATERIAL	COPPER ALLOY CDA 725
CONTACT (GOLD) PLATING	.000050" THICK GOLD OVER NICKEL IN CONTACT ENGAGEMENT AREA
CONTACT (TIN) PLATING	.000100 — .00200 MATTE TIN OVER .00050 MIN. NICKEL
CURRENT RATING	3 AMPS
HOUSING	GLASS FILLED POLYESTER 94V-0 RATED SINGLE ROW: UP TO 32 CONTACTS

1. ASSEMBLY LENGTH TO BE, END OF INSULATION TO END OF INSULATION OR MATING FACE OF CONNECTOR, OR MATING FACE TO MATING FACE.
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230—702.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN E.C. CLAYBAUGH 18/JAN/02		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608									
DIMENSIONS: INCHES			CHK F.MCCORKEL 05/JUN/02		NAME FLEXPAC, GENERIC DRAWING — —									
			APVD F.D. McCORKEL 12/MAR/03											
			PRODUCT SPEC —											
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
			WEIGHT —		A2		00779		C=1474505		—			
MATERIAL —			FINISH —		CUSTOMER DRAWING				SCALE N.T.S.		SHEET 6 of 7		REV D	

D

C

B

A

1474505

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
			—	SEE SHEET 1	—	—

D

C

B

A



- NOTE:
1. ALL TERMINATION CRIMP TINS SHALL MAKE CONTACT WITH THE CONDUCTOR.
 2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN E.C. CLAYBAUGH 18/JAN/02		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES			CHK F.MCCORKEL 05/JUN/02		NAME FLEXPAC, GENERIC DRAWING — —			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD F.D. McCORKEL 12/MAR/03					
	0 PLC ± —		PRODUCT SPEC —					
	1 PLC ± —		APPLICATION SPEC —					
	2 PLC ± —		—					
MATERIAL —	3 PLC ± —		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C=1474505	RESTRICTED TO —
	4 PLC ± —		—					
	ANGLES ± —		—					
FINISH —			CUSTOMER DRAWING		SCALE N.T.S.		SHEET 7 of 7	REV D