

Customer Information Sheet

DRAWING No.: D9XXX-XX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

PART No.	No. OF CONTACTS	No. OF CENTRE BARS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
D9206-01	6	0	7.62	5.08	10.16	7.62
D9208-01	8	0	10.16	7.62	10.16	7.62
D9214-01	14	0	17.78	15.24	10.16	7.62
D9216-01	16	0	20.32	17.78	10.16	7.62
D9218-01	18	0	22.86	20.32	10.16	7.62
D9220-01	20	1	25.40	22.86	10.16	7.62
D9222-01	22	1	27.94	25.40	12.70	10.16
D9224-01	24	1	30.48	27.94	17.78	15.24
D9228-01	28	1	35.62	33.02	17.78	15.24
D9232-01	32	1	40.64	38.10	17.78	15.24
D9240-01	40	2	50.80	48.26	17.78	15.24
D9248-01	48	2	60.96	58.42	25.28	22.86
D9264-01	64	2	81.28	78.74	25.28	22.86
D9724-01	24	1	30.48	27.94	12.70	10.16
D9922-01	22	1	27.94	25.40	10.16	7.62
D9924-01	24	0	30.48	27.94	10.16	7.62
D9948-01	48	2	60.96	58.42	17.78	15.24

SPECIFICATION:

MATERIAL:

MOULDING:

01 FINISH = GLASS-FILLED POLYESTER UL94V-0, BLACK

46 FINISH = HIGH TEMP. POLYAMIDE 46, UL94V-0, BLACK

CONTACTS = BRASS

FINISH:

CONTACTS = 3.5-5.0µ 100% TIN OVER 2µ NICKEL

ELECTRICAL:

CURRENT RATING AT 25°C = 1.5A

CURRENT RATING AT 85°C = 0.25A

CONTACT RESISTANCE (INITIAL) = 15 mΩ MAX

CONTACT RESISTANCE (AFTER CONDITIONING) = 23 mΩ MAX

INSULATION RESISTANCE (INITIAL) = 1,000 MΩ MIN

INSULATION RESISTANCE (AFTER CONDITIONING) = 100 MΩ MIN

ENVIRONMENTAL:

TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

TUBE

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C004XX (LATEST ISSUE)

NOTES:

1. RECOMMENDED PCB HOLE SIZE = Ø0.80mm MIN.

ORDER CODE:

D9XXX-XX

PITCH CODE
SEE TABLE


TOTAL No. OF CONTACTS

FINISH:


01 = 100% TIN

46 = 100% TIN (HIGH TEMP MOULD)


ILLUSTRATION OF
NUMBER OF CENTRE BARS
(SEE TABLE)





0 BARS



1 BAR



2 BARS



JMB 11 18.04.06 9163

NAME ISS. DATE C/NOTE

APPROVED: *[Signature]*

CHECKED: *[Signature]*

DRAWN: P. COLLINS

CUSTOMER REF.:

ASSEMBLY DRG:

HARWIN

HARWIN INC U.S.A. TEL: (812) 542 2540 FAX: (812) 542 2541	HARWIN PLC U.K. TEL: 023 9231 4545 FAX: 023 9231 4590	HARWIN PTE SINGAPORE TEL: 65 6779 4909 FAX: 65 6779 3868
--	--	---

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm

X.X = ±0.25mm

X.XX = ±0.10mm

X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

DIL I.C. THROUGH
HEADER ASSEMBLY

DRAWING NUMBER:

D9XXX-XX

SHT
2 OF 2