

BIDIRECTIONAL MONOLITHIC TVS DIODE ARRAY

APPLICATIONS

- ✓ Multiple I/O Port Protection
- ✓ Board Level Interface Connection
- ✓ RS-232, RS-422 & RS-423
- ✓ Portable Electronics

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns
- ✓ 61000-4-5 (Surge): 12A, 8/20 μ s - Level 1(Line-Gnd) & Level 2(Line-Line)

FEATURES


- ✓ 450 Watts Peak Pulse Power per Line ($t_p = 8/20 \mu$ s)
- ✓ ESD Protection > 40 kilovolts
- ✓ 8 Bidirectional Lines (Monolithic Design)
- ✓ Designed for I/O Protection
- ✓ Available in 4 Voltage Types Ranging from 5.0V to 24V

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SO-14 Package
- ✓ Weight 0.15 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 16mm Tape and Reel Per EIA Standard 481
- ✓ Device Marking: Marking Code & Logo
- ✓ Pin 1 Indicated By DOT on Top of Package



CIRCUIT DIAGRAM






PSMDA05C-8 thru PSMDA24C-8

DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	450	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER (See Note 1)	DEVICE MARKING CODE	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_p = 1A$ V_C VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20 μs $V_C @ I_{PP}$	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_D μA	MAXIMUM CAPACITANCE 0V @ 1 MHz C pF
PSMDA05C-8	SEB	5.0	6.0	9.8	15.4V @ 30A	100	350
PSMDA12C-8	SED	12.0	13.4	19.0	26.4V @ 17A	1	150
PSMDA15C-8	SEF	15.0	16.7	24.0	32.4V @ 14A	1	120
PSMDA24C-8	SEH	24.0	26.7	40.0	45.0V @ 10A	1	100

GRAPHS



PSMDA05C-8 thru PSMDA24C-8

PACKAGE OUTLINE & DIMENSIONS



PART NUMBER SUFFIXES USED FOR TAPE & REEL/BULK ORDERING:

Surface mount product is taped and reeled in accordance with EIA-481.
 Suffix-T7 = 7 Inch Reel - 1,000 pieces per reel i.e.: PSMDA05C-8-T7
 Suffix-T13 = 13 Inch Reel - 2,500 pieces per reel i.e.: PSMDA05C-8-T13
 No Suffix = Product Shipped in Tubes of 55 pcs per Tube

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282

Tel: 602-431-8101 Fax: 602-431-2288

E-Mail: sales@protekdevices.com

Web Site: www.protekdevices.com