




SERIES 337/387



FEATURES

UL Recognized

.156 (3.96) Contact Spacing x .200 (5.08) Row Spacing

Accepts .062 (1.57) Nominal Thickness P.C. Board

High Profile Insulator Body, .600 (15.24)

Contact Termination Options include P.C Tail, Wire Hole, Wire Wrap, 90 Degree & Extender Board Bends

Single or Dual Row Configurations

Large Variety of Mounting Options, Flush or Offset Lugs

Pre-assembled Card Guides Available

Accepts Between Contact and In-Contact Polarizing Keys

SPECIFICATIONS

Insulator Material: Thermoplastic Polyester, UL 94V-0.

Contact Material: Copper, Nickel, Tin Alloy CA-725

Contact Plating: Gold on the Mating Area, Tin on the

Contact Tails, Nickel Underplate

Current Rating: 3 Amperes Continuous

Contact Resistance: 10 Milliohms Maximum

Dielectric Withstanding Voltage: 1800 V AC rms at Sea Level Between Adjacent Contacts

Insulation Resistance: 5000 Megohms Minimum

Operating Temperature: -65 to +105 Degrees C

Insertion Force: 16 oz (4.45 N) Maximum per Contact Pair when Tested with a .070 (1.78) Thick Gauge

Withdrawal Force: 1 oz (.28 N) Minimum per Contact Pair when Tested with a .054 (1.37) Thick Gauge

Example Part Number 337 - 086 - 524 - 2 04

Series _____
Total Number of Contacts _____
Contact Code _____
Contact Rows and Insulator Style _____
Mounting Options _____





Series	Insulator Colour	
337	Green	
387	Black	
Total Number of Contacts		Contact Rows
006, 007, ..., 043		Single Row
012, 014, ..., 086		Dual Row
Contact Code	Description & Tail Size	Tail Length "G"
500 Wire Hole	.050 x .025 (1.27 x 0.64)	.260 (6.60)
520 P.C. Tail	.030 x .018 (0.76 x 0.46)	.175 (4.45)
521 P.C. Tail	.025 Square (0.64 Square)	.150 (3.81)
523 P.C. Tail	.025 Square (0.64 Square)	.390 (9.91)
524 P.C. Tail	.018 Square (0.46 Square)	.175 (4.45)
540 Wire Wrap	.025 Square (0.64 Square)	.560(14.22)
541 Wire Wrap	.025 Square (0.64 Square)	.750(19.05)
542 Wire Wrap	.025 Square (0.64 Square)	.645(16.38)
544 Wire Wrap	.050 x .025 (1.27 x 0.64)	.750(19.05)
555	Extender Board Bend (Code 500 Contacts)	
556	Extender Board Bend (Code 520 Contacts)	
558	90 Degree Bend (Code 541 Contacts)	
559	90 Degree Bend (code 541 Contacts)	
560	Extender Board Bend (Code 523 Contacts)	

Contact Rows and Insulator Style	Description
1	Single Row, Flush Mounting Lugs
2	Dual Row, Flush Mounting Lugs
6	Single Row, .170 (4.32) Offset Lugs
8	Dual Row, .170 (4.32) Offset Lugs

Mounting Options	Description
01	No Mounting Lugs
02	.128 (3.25) Dia. Mounting Holes
03	.116 (2.95) I.D. Floating Eyelets
04	.156 (3.96) Dia. Mounting Holes
07	M3-0.5 Metric Threaded Inserts
08	#4-40 Unified Threaded Inserts
12	.128 (3.25) Dia. Side Mounting Holes
58	.468 (11.89) Offset Card Guides
78	In-Line Card Guides

Ordering Code Notes

- 1) All connector sizes up to 43 contacts single row / 86 contacts dual row are available upon request
- 2) The 500 contact code is standard in the 337 series only. Diallyl Phthalate insulator material will be supplied
- 3) For lugless connectors, code 01 mounting, specify contact rows codes 1 or 2
- 4) In-Line card guides are only available with offset mounting lugs




CONNECTOR MOUNTING PATTERN

BETWEEN CONTACT
POLARIZING KEY
P/N 306-240-318






IN-CONTACT
POLARIZING KEY
P/N 343-240-328



SINGLE ROW

DUAL ROW



RECOMMENDED DAUGHTER BOARD

NUMBER OF CONTACTS		"A"		"B"		"C"		"D"		"E"	
Single	Dual	Inch	(mm)	Inch	(mm)	Inch	(mm)	Inch	(mm)	Inch	(mm)
6	12	1.842	(46.79)	1.532	(38.91)	1.246	(31.65)	1.100	(27.94)	.780	(19.81)
10	20	2.466	(62.64)	2.156	(54.76)	1.870	(47.50)	1.724	(43.79)	1.404	(35.66)
12	24	2.778	(70.56)	2.468	(62.69)	2.182	(55.42)	2.036	(51.71)	1.716	(43.59)
15	30	3.246	(82.45)	2.936	(74.57)	2.650	(67.31)	2.504	(63.60)	2.184	(55.47)
18	36	3.714	(94.34)	3.404	(86.46)	3.118	(79.20)	2.972	(75.49)	2.652	(67.36)
22	44	4.338	(110.19)	4.028	(102.31)	3.742	(95.05)	3.596	(91.34)	3.276	(83.21)
25	50	4.806	(122.07)	4.496	(114.20)	4.210	(106.93)	4.064	(103.23)	3.744	(95.10)
26	52	4.962	(126.03)	4.652	(118.16)	4.366	(110.90)	4.220	(107.19)	3.900	(99.06)
28	56	5.274	(133.96)	4.964	(126.09)	4.678	(118.82)	4.532	(115.11)	4.212	(106.98)
31	62	5.742	(145.85)	5.432	(137.97)	5.146	(130.71)	5.000	(127.00)	4.680	(118.87)
33	66	6.054	(153.77)	5.744	(145.90)	5.458	(138.63)	5.312	(134.92)	4.992	(126.80)
36	72	6.522	(165.66)	6.212	(157.78)	5.926	(150.52)	5.780	(146.81)	5.460	(138.68)
43	86	7.614	(193.40)	7.304	(185.52)	7.018	(178.26)	6.872	(174.55)	6.552	(166.42)

Dimensions of Other Connector Sizes are Listed

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[337-012-524-802](#) [337-020-524-802](#) [337-024-524-802](#) [337-030-524-802](#) [337-036-524-802](#) [337-044-524-802](#) [337-050-524-802](#) [337-056-524-802](#) [337-060-524-802](#) [337-072-524-802](#) [337-086-524-802](#) [337-006-520-102](#) [337-012-500-202](#) [337-012-520-201](#) [337-012-521-201](#) [337-012-521-202](#) [337-012-523-202](#) [337-012-524-201](#) [337-012-540-202](#) [337-012-541-202](#) [337-012-542-202](#) [337-020-500-201](#) [337-020-500-202](#) [337-020-520-201](#) [337-020-520-202](#) [337-020-521-201](#) [337-020-521-202](#) [337-020-523-202](#) [337-020-524-201](#) [337-020-540-201](#) [337-020-540-202](#) [337-020-540-802](#) [337-020-541-202](#) [337-020-542-202](#) [337-024-500-202](#) [337-024-520-201](#) [337-024-520-202](#) [337-024-521-201](#) [337-024-521-202](#) [337-024-540-201](#) [337-024-540-202](#) [337-024-541-202](#) [337-030-500-202](#) [337-030-500-204](#) [337-030-520-201](#) [337-030-520-202](#) [337-030-521-201](#) [337-030-521-202](#) [337-030-523-201](#) [337-030-523-802](#) [337-030-524-201](#) [337-030-524-202](#) [337-030-527-201](#) [337-030-540-201](#) [337-030-540-202](#) [337-030-540-802](#) [337-030-541-202](#) [337-030-541-802](#) [337-032-500-202](#) [337-036-500-202](#) [337-036-500-204](#) [337-036-520-201](#) [337-036-520-202](#) [337-036-520-204](#) [337-036-521-201](#) [337-036-521-202](#) [337-036-521-802](#) [337-036-523-202](#) [337-036-524-201](#) [337-036-527-202](#) [337-036-540-202](#) [337-036-540-802](#) [337-036-541-201](#) [337-036-541-202](#) [337-044-500-202](#) [337-044-500-204](#) [337-044-500-802](#) [337-044-520-201](#) [337-044-520-202](#) [337-044-520-802](#) [337-044-521-201](#) [337-044-521-202](#) [337-044-521-204](#) [337-044-521-300](#) [337-044-521-802](#) [337-044-523-202](#) [337-044-524-201](#) [337-044-524-202](#) [337-044-524-204](#) [337-044-527-201](#) [337-044-540-201](#) [337-044-540-202](#) [337-044-540-204](#) [337-044-540-802](#) [337-044-541-201](#) [337-044-541-202](#) [337-044-541-204](#) [337-044-541-802](#) [337-044-542-201](#) [337-044-542-202](#)