



PROTEK DEVICES
Only One Name Means ProTek'Tion™

ULC0402FC3.3C
thru
ULC0402FC24C

UNBUMPED LOW CAPACITANCE FLIP CHIP ARRAY

APPLICATIONS

- ✓ Cellular Phones
- ✓ Personal Digital Assistant (PDA)
- ✓ Notebook Computers
- ✓ SMART Cards

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns

FEATURES


- ✓ ESD Protection > 25 kilovolts
- ✓ Available in Six Voltage Types Ranging From 3.3V to 24V
- ✓ 200 Watts Peak Pulse Power per Line ($t_p = 8/20\mu s$)
- ✓ Low Clamping Voltage
- ✓ Bidirectional Configuration & Monolithic Structure
- ✓ Protects 1 Line
- ✓ **LOW CAPACITANCE**
- ✓ **LOW LEAKAGE CURRENT**

MECHANICAL CHARACTERISTICS

- ✓ Standard EIA Chip Size: 0402
- ✓ Weight 0.73 milligrams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 8mm Plastic & Paper Tape and Reel Per EIA Standard 481
- ✓ Device Marking On Reel



PIN CONFIGURATION



DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified



PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	200	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified





PART NUMBER (See Note 1)	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_p = 1A$ V_C VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20 μs V_C @ I_{PP}	MAXIMUM LEAKAGE CURRENT (See Note 2) @ V_{WM} I_D μA	TYPICAL CAPACITANCE @ 0V, 1 MHz C pF
ULC0402FC3.3C	3.3	4.0	7.0	12.5V @ 16A	75*	70
ULC0402FC05C	5.9	6.0	11.0	13V @ 15A	10**	35
ULC0402FC08C	8.0	8.5	13.2	18V @ 11A	1	32
ULC0402FC12C	12.0	13.3	19.8	26.9V @ 7.4A	1	30
ULC0402FC15C	15.0	16.7	25.4	34.5V @ 5.8A	1	25
ULC0402FC24C	24.0	26.7	37.2	50.6V @ 4A	1	20

Note 1: All devices are bidirectional. Electrical characteristics apply in both directions.

Note 2: *Maximum leakage current < 5 μA @ 2.8V. **Maximum leakage current < 500nA @ 3.3V.



GRAPHS



PACKAGE OUTLINE & DIMENSIONS

PACKAGE OUTLINE TOP SIDE END Metalized Die Contacts	U0402 PACKAGE DIMENSIONS <table><tr><th>DIM</th><th>MILLIMETERS</th><th>INCHES</th></tr><tr><td>A</td><td>0.46 NOM</td><td>0.018 NOM</td></tr><tr><td>B</td><td>0.86 NOM</td><td>0.034 NOM</td></tr><tr><td>C</td><td>0.99 ± 0.0254</td><td>0.039 ± 0.001</td></tr><tr><td>D</td><td>0.10 NOM</td><td>0.004 NOM</td></tr><tr><td>E</td><td>0.35 NOM</td><td>0.014 NOM</td></tr><tr><td>F</td><td>0.483 ± 0.0254</td><td>0.019 ± 0.001</td></tr><tr><td>I</td><td>0.406 NOM</td><td>0.016 NOM</td></tr></table> NOTES: 1. Controlling dimensions in inches. 2. Decimal tolerances for mounting pad and outline: .xxx ± 0.05mm (± 0.002"). 3. Maximum chip size: 1.02 (0.040") by 0.51(0.020").	DIM	MILLIMETERS	INCHES	A	0.46 NOM	0.018 NOM	B	0.86 NOM	0.034 NOM	C	0.99 ± 0.0254	0.039 ± 0.001	D	0.10 NOM	0.004 NOM	E	0.35 NOM	0.014 NOM	F	0.483 ± 0.0254	0.019 ± 0.001	I	0.406 NOM	0.016 NOM						
DIM	MILLIMETERS	INCHES																													
A	0.46 NOM	0.018 NOM																													
B	0.86 NOM	0.034 NOM																													
C	0.99 ± 0.0254	0.039 ± 0.001																													
D	0.10 NOM	0.004 NOM																													
E	0.35 NOM	0.014 NOM																													
F	0.483 ± 0.0254	0.019 ± 0.001																													
I	0.406 NOM	0.016 NOM																													
MOUNTING PAD DIE SOLDER PAD DIE CONTACTS SOLDER PRINT DIAMETER 0.010" - 0.012"	PAD DIMENSIONS <table><tr><th>DIM</th><th>MILLIMETERS</th><th>INCHES</th></tr><tr><td>A</td><td>0.23</td><td>0.009</td></tr><tr><td>B</td><td>0.48</td><td>0.019</td></tr><tr><td>C</td><td>0.69</td><td>0.027</td></tr><tr><td>D</td><td>0.46</td><td>0.018</td></tr><tr><td>E</td><td>0.99</td><td>0.039</td></tr><tr><td>F</td><td>0.20</td><td>0.008</td></tr><tr><td>G</td><td>0.20</td><td>0.008</td></tr><tr><td>H</td><td>0.66</td><td>0.026</td></tr><tr><td>I</td><td>0.13</td><td>0.005</td></tr></table> NOTE: 1. Top view of tape. Metal contacts are face down in tape package. TAPE & REEL ORIENTATION Single Die - 0402 NOTE: 1. Preferred: Using 0.1mm (0.004") stencil. Outline & Dimensions: Rev 3 - 11/02, 06020	DIM	MILLIMETERS	INCHES	A	0.23	0.009	B	0.48	0.019	C	0.69	0.027	D	0.46	0.018	E	0.99	0.039	F	0.20	0.008	G	0.20	0.008	H	0.66	0.026	I	0.13	0.005
DIM	MILLIMETERS	INCHES																													
A	0.23	0.009																													
B	0.48	0.019																													
C	0.69	0.027																													
D	0.46	0.018																													
E	0.99	0.039																													
F	0.20	0.008																													
G	0.20	0.008																													
H	0.66	0.026																													
I	0.13	0.005																													
TAPE & REEL ORDERING NOMENCLATURE 1. Surface mount product is taped and reeled in accordance with EIA 481. 2. 8mm Plastic Tape: 7 Inch Reels - 5,000 pieces per reel. Ordering Suffix: -T75-1 (i.e., ULC0402FC05C-T75-1). 3. 8mm Paper Tape: 7 Inch Reels - 10,000 pieces per reel. Ordering Suffix: -T710-2 (i.e., ULC0402FC05C-T710-2).																															

TAPE & REEL ORDERING NOMENCLATURE

- Surface mount product is taped and reeled in accordance with EIA 481.
- 8mm Plastic Tape: 7 Inch Reels - 5,000 pieces per reel. Ordering Suffix: -T75-1 (i.e., ULC0402FC05C-T75-1).
- 8mm Paper Tape: 7 Inch Reels - 10,000 pieces per reel. Ordering Suffix: -T710-2 (i.e., ULC0402FC05C-T710-2).

COPYRIGHT © ProTek Devices 2003
SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.

ProTek Devices

2929 South Fair Lane, Tempe, AZ 85282
Tel: 602-431-8101 Fax: 602-431-2288
E-Mail: sales@protekdevices.com
Web Site: www.protekdevices.com