








MICRO SWITCH
A DIVISION OF MINNEAPOLIS HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS
FED. MFR. CODE 91929

SWITCH - ENCLOSED

CATALOG LISTING
2LN1-5-RH



NOTE—
▲ DOWEL HOLES WILL ACCEPT .187 MAX DIA DOWEL PINS
ON 3.250 X .375 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE ———	3 LB MAX	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
DIFFERENTIAL FORCE ———	1/4 LB MIN	(SEE CIRCUIT DIAGRAM)		
RELEASE FORCE ———	1/2 LB MIN			UNLESS OTHERWISE SPECIFIED
PRETRAVEL ———	.125 MAX			DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL ———	.078 MAX	-L25- 10 A-125 OR 250 VAC		TOLERANCES ARE:
OVERTRAVEL ———	.344 MIN	1/2 HP-125 VAC		ONE PLACE (.0) ± .030
				TWO PLACE (.00) ± .015
				THREE PLACE (.000) ± .005
				ANGLES ±
				WEIGHT