







Part Number	Emitting Color	Emitting Material	Luminous Intensity (IF=10mA) mcd	Wavelength nm λ P	Description
			min.	typ.	
DMR08A	Red	GaAlAs	4700	19990	660 Common Anode, Rt. Hand Decimal.
Published Date : MAR 05,2008					
Drawing No : SDSA2017		V4		Checked : Shin Chi	
P.1/4					



❖ **MR**



Wave Soldering Profile For Lead-free Through-hole LED.



NOTES:

1. Recommend the wave temperature $245^{\circ}\text{C} \sim 260^{\circ}\text{C}$. The maximum soldering temperature should be less than 260°C .
2. Do not apply stress on epoxy resins when temperature is over 85°C .
3. The soldering profile apply to the lead free soldering (Sn/Cu/Ag alloy).
4. No more than once.

Remarks:


If special sorting is required (e.g. binning based on forward voltage, luminous intensity/ luminous flux or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: $\pm 1\text{nm}$
2. Luminous Intensity/ luminous flux: $\pm 15\%$
3. Forward Voltage: $\pm 0.1\text{V}$


Note: Accuracy may depend on the sorting parameters.

PACKING & LABEL SPECIFICATIONS

DMR08A



Inside LABEL Paste On The IC-tube



Outside LABEL Paste On The Box

