



## EPOXY COATED, NON-INDUCTIVE, METALLIZED FILM CAPACITORS, RADIAL LEAD

## FEATURES

- ☐ VERY SMALL SIZE, HIGHLY RELIABLE BECAUSE OF ITS SELF-HEALING PERFORMANCE
- ☐ COATED WITH EPOXY RESIN FOR SUPERIOR HEAT RESISTANCE, HUMIDITY RESISTANCE AND SOLVENT RESISTANCE
- ☐ RECOMMENDED FOR USE WITH FILTERING, DC BLOCKING, AND COUPLING COMMUNICATIONS EQUIPMENT.

## SPECIFICATIONS

|                             |                                                             |
|-----------------------------|-------------------------------------------------------------|
| OPERATING TEMPERATURE RANGE | -55°C to +125°C with voltage derating of 1.25% per degree C |
| RATED VOLTAGE (DC)          | 250V, 400V, 630V                                            |
| CAPACITANCE RANGE           | 0.01 to 4.7 MFD                                             |
| CAPACITANCE TOLERANCE       | ±10% (K), ±5% (J)                                           |
| INSULATION RESISTANCE       | C < 0.33 MFD. R ≥ 15,000 MEGOHM                             |
|                             | C ≥ 0.33 MFD. RC ≥ 5,000 MEGOHM X MFD                       |
| DISSIPATION FACTOR          | ≤ 0.007 (at 1 KHz, 25°C)                                    |
| DIELECTRIC STRENGTH         | 150% of rated voltage for 5 seconds                         |



### STANDARD PRODUCTS AND CASE SIZE TABLE (UNIT: mm)

[illegible]

Special sizes & capacitance values are available upon request.