


© 1962 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING. APPROVED PER GOVT CONTRACT NO.

LOCATION FOR AMP-TAB FEMALE CONTACT

CAVITY IDENTIFICATION ON TOP SURFACE OF HOUSING.
P/N (I)-582589-1 ONLY.

(I)-582589-1. SAME AS -1 EXCEPT TO HAVE CAVITY IDENTIFICATION ON TOP SURFACE OF HOUSING.

REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
Y		ECO-08-020973	11-08
			APPROVED JW



3. LASER MARKING ACCEPTABLE FOR ALL MARKING

- GROOVES FOR "ON CONTACT KEYING" AMP'S OPTION DEPENDING ON METHOD OF MANUFACTURE. FOR "ON CONTACT" KEYING USE KEYING PLUG P/N 583487-1. (MUST BE ORDERED SEPARATELY.)
- MOUNTING EAR CONFIGURATION AMP'S OPTION DEPENDS ON METHOD OF MANUFACTURE.

582589-1. AS SHOWN "J" DIA HOLES = .128


OBS 582589-2. 1. SAME AS -1 EXCEPT 2. "J" DIA HOLES = .156

OBS 582589-6. SAME AS -4 EXCEPT INK STAMPING ON TOP AND BOTTOM


OBSOLETE 582589-4. 1. SAME AS -1 EXCEPT: 2. FLOATING BUSHINGS.

OBS 582589-5. 1. SAME AS -4 EXCEPT: FLOATING BUSHINGS REVERSED.


CLEARANCE FOR #4 SCREW.



-4 BUSHING REVERSED AS SHOWN



SECTION A-A



ALTERNATE MOUNTING EAR CONFIGURATION

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		CONTRACT NO.		AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
FRACTIONS	DECIMALS	DR	DATE	NAME	
± .005	± .005	J. Asch	12-16-66	22 POSITION	
MATERIAL	HEAT TREAT	CHK	DATE	AMP-TAB CONNECTOR	
SEE CALLOUT	SEE CALLOUT	W. Bump	1-5-67	.100 CENTERS QUAD	
FINISH	OTHER APPD	DSGN ENGR	DATE	SIZE	CODE IDENT NO
SEE CALLOUT		J. Kaufman	1-11-67	C	00779
		R. Showman	1/10/67	NUMBER	REV
				582589	Y
		SCALE 4-1		WT	CALC
		ACTUAL		SHEET	

CUSTOMER DRAWING