

D15LC20U

200V 15A

FEATURES

- Low noise
- trr35ns
- Fully Isolated Molding


APPLICATION

- Switching power supply
- Free Wheel
- Home Appliances, Office Equipment
- Telecommunication, Factory Automation

OUTLINE DIMENSIONS

Case : ITO-220

Unit : mm



RATINGS


● Absolute Maximum Ratings (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		200	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load, Rating for each diode IO/2, Tc=104°C	15	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	110	A
Dielectric Strength	Vdis	Terminals to case, AC 1 minute	1.5	kV
Mounting Torque	TOR	(Recommended torque: 0.3N·m)	0.5	N·m


● Electrical Characteristics (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=7.5A, Pulse measurement, Rating of per diode	Max 0.98	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max 10	μA
Reverse Recovery Time	trr	IF=0.5A, IR=1A, Rating of per diode	Max 35	ns
Thermal Resistance	θjc	junction to case	Max 2.8	°C/W
	θjf	junction to heatsink (reference value)	Max 4.3	


D15LC20U Forward Voltage



D15LC20U Forward Power Dissipation




$T_j = T_{jmax}$




D15LC20U


Derating Curve



$$V_R = V_{RM}$$



D15LC20U Peak Surge Forward Capability



D15LC20U Junction Capacitance

