

DESIGNED TO IEC STANDARD

5 x 20 mm Time Lag Fuse (Slo-Blo® Type Fuse)



- Designed to International (IEC) Standards for use globally.
- Meets the IEC 127-2, Sheet 6 specification for Time Lag Fuses.
- Available in Cartridge and Axial Lead Format.
- Available in ratings of 0.125 to 6.3 amperes.

ELECTRICAL CHARACTERISTICS:

% of Ampere Rating	Opening Time
150%	60 minutes, Minimum
210%	2 minutes, Maximum
275%	0.6 sec., Min. ; 10 sec. Max
400%	.15 sec., Min. ; 3 sec. Max
1000%	0.02 sec., Min. ; 0.3 sec. Max.

AGENCY APPROVALS: Sheet 6 IEC 127: SEMKO, BSI and VDE approved. Recognized 1A to 6.3A under the components program of Underwriters Laboratories and recognized by CSA. MITI A 1A to 6.3A.

INTERRUPTING RATINGS: 150 amperes

PACKAGING: For Axial Leads add packaging suffix XE.

ORDERING INFORMATION:

Catalog Number	Ampere Rating	Nominal Voltage Rating	Nominal Resistance Cold Ohms	Nominal Melting I ² t A ² Sec
0219.125	.125	250	4.41	0.150
0219.160	.160	250	2.44	0.225
0219.200	.200	250	1.60	0.350
0219.250	.250	250	1.05	0.555
0219.315	.315	250	0.848	1.14
0219.400	.400	250	0.535	1.35
0219.500	.500	250	0.370	2.90
0219.630	.630	250	0.275	4.80
0219.800	.800	250	0.163	9.42
0219.001.	1	250	0.055	3.33
0219 1.25	1.25	250	0.042	5.80
0219 01.6	1.6	250	0.032	10.61
0219 002.	2	250	0.029	14.80
0219 02.5	2.5	250	0.022	23.85
0219 3.15	3.15	250	0.017	39.20
0219 004.	4	250	0.013	70.95
0219 005.	5	250	0.010	114.0
0219 06.3	6.3	250	0.0075	204.0

