

UNO-2171

Intel® Pentium® M/Celeron® M UNO
with 2 x LAN, 4 x COM, PC/104+



Features

- Onboard Pentium® M 1.4 GHz or Celeron® M 1.0 GHz
- Onboard 512 KB battery-backup SRAM
- Two RS-232 and two RS-232/422/485 ports with automatic flow control.
- Two 10/100Base-T RJ-45 ports
- Audio with Mic in, Line in, Line out
- Two USB and one type I/II PC Card
- PC/104+ expansion slots
- Windows® CE 5.0 & 6.0, Windows XP Embedded SP2, and Linux ready solution
- Onboard system status LED indicators
- Supports Wake On LAN and Boot From LAN function
- Fanless and no internal cabling design

Introduction

UNO-2171 is an embedded automation computer that supports PC/104+ expansion, serial communication ports and several other networking interfaces. UNO-2171 supports Windows XP Embedded OS and Windows CE 5.0 & 6.0, which offers a pre-configured image with optimized onboard device drivers. Windows XP Embedded delivers the power of the Windows operating system in componentized form. You can seamlessly integrate your applications into Windows XP Embedded and speed up your system development with an application ready platform that can provide a rich networking interface to fulfill diverse requirements.

Specifications

General

- **Certifications** CE, FCC class A, UL, CCC
- **Dimensions (W x D x H)** 255 x 152 x 59 mm (10" x 6.0" x 2.3")
- **Enclosure** Aluminum
- **Mounting** Wall
- **Power Consumption** 24 W (Typical)
- **Power Input** 10 ~ 53 V_{DC} (e.g. +24 V @ 2 A) (Min. 48 W), ATX
- **Weight** 2.4 kg (Typical)
- **OS Support** Windows XP Embedded, Windows 2000/XP, Windows CE 5.0 & 6.0, Linux

System Hardware

- **CPU** Pentium M 1.4 GHz, Celeron M 1.0 GHz
- **Memory** 512 MB/1 GB DDR SDRAM
- **Battery Backup SRAM** 512 KB
- **Indicators** LEDs for power, IDE, alarm for RAM backup battery,
- **Keyboard/Mouse** 1 x PS/2
- **PC Card** 1 x PC Card slot, supports CardBus (Card-32) Card and 16-bit (PCMCIA 2.1/JEIDA4.2) card Supports +5 V, +3.3 V
- **PC/104+** PC/104+ slot, Supports +5 & 3.3 V Power
- **Storage** SSD: 2 x internal type I/II CompactFlash® slot
HDD: one standard 2.5" HDD
- **VGA** DB15 VGA connector, 1600 x 1200 @ 85 Hz
- **Audio** Mic in, Line in, Line out
- **Watchdog Timer** Programmable

Communications

- **Serial Ports** 2 x RS-232, 2 x RS-232/422/485 with DB9 connectors Automatic RS-485 data flow control
- **Serial Port Speed** RS-232: 50 ~ 115.2 kbps
RS-422/485: 50 ~ 921.6 kbps (Max.)
- **LAN** 2 x 10/100Base-T RJ-45 ports (supports wake on LAN and built-in boot ROM in flash BIOS)
- **USB Ports** 2 x USB, EHCI, Rev. 2.0 compliant

Environment

- **Humidity** 95% @ 40° C (non-condensing)
- **Operating Temperature** -20 ~ 65° C (-4 ~ 149° F) @ 5 ~ 85% RH
- **Shock Protection** IEC 68 2-27
CompactFlash: 50 G @ wall mount, half sine, 11 ms
HDD: 20 G @ wall mount, half sine, 11 ms
- **Vibration Protection** IEC 68 2-64 (Random 1 Oct./min, 1hr/axis.)
CompactFlash: 2 Grms @ 5 ~ 500 Hz,
HDD: 1 Grms @ 5 ~ 500 Hz

Ordering Information

- **UNO-2171-C11E** C-M 1.0 G, 512 MB RAM UNO-2171
- **UNO-2171-P12E** P-M 1.4 G, 1 GB RAM UNO-2171

Accessories

- **UNO-PCM22-AE** 2 x PC/104 expansion kit
- **UNO-FPM21-AE** UNO & FPM integration kit