





PRODUCT NUMBER
71977-Y08LF

ROHS COMPATIBLE, SEE NOTE 5
NUMBER OF POSITIONS PER ROW
PLATING :

3=0.76µm GOLD/GXT ON CONTACT AREA
2 µm Min MATTE TIN ON TAIL
4=2µm MIN MATTE TIN FULL PLATED
1.27µm Ni MIN UNDERPLATING

NOTES :

1. HOUSING MAT'L : GLASS FILLED THERMOPLASTIC
UL94V-0 COLOR: BLUE
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. 22N MIN PIN RETENTION IN EITHER DIRECTION
4. PRODUCTS PACKED IN POLYBAGS
5. ROHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code		SEE NOTE		surface		tolerance		projection		product family	
ltr	ecn no	dr	date	ISO 1302	ISO 406	ISO 1101	ISO 1101	mm	mm	DBX HDR	DBX HDR
A	10922	FMU	89.05.24	tolerances unless otherwise specified							
B	F06-0107	LMU	06.01.13	linear							
C	F06-0228	LMU	06.07.11								
D	F08-0147	YOV	08.04.14	dr	LMULN		06.01.13	scale 4:1			
E	B-19286	AMA	14.11.03	engf	JM.C		06.01.13				
				chr							
				apptd	JM.C		06.01.13				
sheet		revision									
index		sheet									



SPECIAL HDR

DUBOX HEADER 4 WALLS

71977

CUSTOMER Drawing

A3



FCIconnect.com

Copyright FCI