


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		P2	REVISED PER ECO-11-004820	11MAR11	RK	HMR



- 1

HOUSING: PBT, UL 94V-0 RATED, COLOR-BLACK
CONTACTS: COPPER ALLOY PER ASTM B103
- 2

MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- 3

0.00076[.000030] MIN GOLD IN CONTACT AREA, 0.00127-0.00254[.000050-.000100]
TIN-LEAD IN AREA E, ALL OVER 0.00127[.000050] MIN NICKEL.
- 4

0.00076 [.000030] MIN GOLD IN CONTACT AREA, 0.00127-0.00254 [.000050-.000100]
TIN IN AREA E, ALL OVER 0.00127[.000050] MIN NICKEL
- 5

USE WITH #26-#22 AWG WIRE SIZE, .050 MAX INSULATION DIA.,
.015 MAX INSULATION WALL THICKNESS.
- 6

CONTACT IDENTIFICATION NUMBER "5" LOCATED IN THIS AREA.
- 7

AMP TRADEMARK (EITHER SIDE).
- 8

ROHS 2002 /95/EC COMPLIANT
- 9

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

9	OBSOLETE	8	4	68.58 [2.700]	26	54	5-102694-9
		8	4	25.40 [1.000]	9	20	5-102694-8
		8	4	22.86 [.900]	8	18	5-102694-7
		8	4	20.32 [.800]	7	16	5-102694-6
		8	4	17.78 [.700]	6	14	5-102694-5
		8	4	15.24 [.600]	5	12	5-102694-4
		8	4	10.16 [.400]	3	8	5-102694-2
		8	4	7.62 [.300]	2	6	5-102694-1
9	OBSOLETE	3		68.58 [2.700]	26	54	102694-9
		3		25.40 [1.000]	9	20	102694-8
9	OBSOLETE	3		22.86 [.900]	8	18	102694-7
		3		20.32 [.800]	7	16	102694-6
9	SUP BY 5-102694-6	3		17.78 [.700]	6	14	102694-5
		3		15.24 [.600]	5	12	102694-4
		3		12.70 [.500]	4	10	102694-3
		3		10.16 [.400]	3	8	102694-2
		3		7.62 [.300]	2	6	102694-1
		FINISH	B	A	NO. OF POSN	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SHUEY 12-30-91		 TE Connectivity					
		CHK M. RIDER 1-6-92							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		AMPMODU MT, RCPT ASSY, HIGH PRESSURE CONTACTS FOR 22-26 AWG WIRE SIZE			
		APVD M. RIDER 1-6-92							
		PRODUCT SPEC 108-25018							
		APPLICATION SPEC 114-25032							
		FINISH		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
		SEE TABLE		A2	00779	C=102694		—	
				CUSTOMER DRAWING		SCALE	4:1	SHEET	1 of 1
								REV	P2