



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

# Customer Specification

## PART NO. 2423C

### Construction

		Diameters (In)			
1) Component 1	3 X 1 COND				
a) Conductor	18 (16/30) AWG TC	0.047			
b) Insulation	0.016" Wall, Nom. Polyethylene(PE)	0.079			
(1) Color(s)					
Cond	Color	Cond	Color	Cond	Color
1	BLACK	2	RED	3	NATURAL
2) Cable Assembly	3 Components Cabled				
a) Twists:	4.8 Twists/foot (min)				
3) Shield:	Alum/Mylar Tape, 25% Overlap, Min.				
a) Foil Direction	Foil Facing Out				
b) Drain Wire	20 (10/30) AWG TC				
4) Jacket	0.020" Wall, Nom.,PVC	0.214 (0.224 Max.)			
a) Color(s)	SLATE				
b) Print	ALPHA WIRE-* P/N 2423C 3C 18 AWG SHIELDED 75C (UL) TYPE CMG OR AWM 2093 ---- C(UL) CMG FT4 ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]				

### Applicable Specifications

1) UL	AWM/STYLE 2093	60°C / 300 V <sub>RMS</sub>
	CMG	75°C
	VW-1	
2) CSA International	C(UL) TYPE CMG	75°C
	FT4	

### Environmental

1) EU Directive 2002/95/EC(RoHS):	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

### Properties

Physical & Mechanical Properties	
1) Temperature Range	-20 to 75°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	46 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V <sub>RMS</sub>
2) Capacitance	23.9 pf/ft @ 1 kHz, Nominal Conductor to Conductor
3) Ground Capacitance	43 pf/ft @ 1 kHz, Nominal
4) Inductance	0.18 µH/ft, Nominal
5) Conductor DCR	7.1 /1000ft @20°C, Nominal
6) OA Shield DCR	8.5 /1000ft @20°C, Nominal

## Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	12 x 10 x 5 Continuous length
b) BOX 1000FT	11-3/4 EASY REEL: Continuous length
c) BOX 500FT	9-1/2 EASY REEL: Continuous length
d) 500 FT	12 x 4.5 x 3.5 Continuous length
e) 328 FT	10 x 4 x 3.5 Continuous length
f) 100 FT	6.5 x 4 x 2.5 Continuous length
<i>[Spool dimensions may vary slightly]</i>	

[www.alphawire.com](http://www.alphawire.com)

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207  
 Tel: 1-800-52 ALPHA (25742), Web: [www.alphawire.com](http://www.alphawire.com)

## RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:2423C

2423C , RoHS-Compliant Commencing With 8/1/2005 Production


*This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European*

Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.**

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	0.1% by weight (1000 ppm)
Including Deca-BDE	0.1% by weight (1000 ppm)

*The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.*

Authorized Signatory for the Alpha Wire Company:



Dave Watson, Director of Engineering & QA

10/31/2012

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[2423C SL002](#)