

Smart-UPS VT

APC Smart-UPS VT 15kVA 400V w/2 Batt. Modules, Start-Up 5X8, Internal Maintenance Bypass

SUVT15KH2B2S

DISCONTINUED : recommended
replacement product
[SUVT15KH2B2](#)



APC Smart-UPS VT, 12 kW / 15
kVA, Input 400V 3PH / Output 230V, 400V 3PH,
Interface Port DB-9 RS-232, Smart-Slot

Includes: Battery modules ship installed, Bolt
down brackets, CD with software, Installation
guide, Smart UPS signalling RS-232 cable, Start
up included, User Manual, Web/SNMP
Management Card

Smart-UPS VT Features & Benefits

Availability	
Dual mains input	Increases availability by allowing the UPS to be connected to two separate power sources.
Scalable runtime	Allows additional run time to be quickly added as needed.
Hot-swappable batteries	Ensures clean, uninterrupted power to protected equipment while batteries are being replaced
Generator Compatible	Ensures clean, uninterrupted power to protected equipment when generator power is used.
Automatic internal bypass	Supplies utility power to the connected loads in the event of a UPS overload condition or fault.
Battery modules connected in parallel	Delivers higher availability through redundant batteries.
Serviceability	
User-replaceable batteries	Increases availability by allowing a trained user to perform upgrades and replacements of the batteries reducing Mean Time to Repair (MTTR)
Battery replacement without tools	Allows quick, easy battery replacement.
Automatic self-test	Periodic battery self-test ensures early detection of a battery that needs to be replaced.
Shippable with modules installed	Enables pre-installation UPS staging and testing and faster installation.
Modular design	Provides fast serviceability and reduced maintenance requirements via self-diagnosing, field-replaceable modules.
Manageability	
Network manageable	Provides remote management of the UPS over the network.
InfraStruXure Manager Compatible	Enables centralized management via the APC InfraStruXure® Manager.
LCD display	Alpha-Numeric Display which displays system parameters and alarms.
Audible Alarms	Provides notification of changing utility power and UPS conditions.
Programmable frequency	Ensures compatibility with different input frequencies.
LED status indicators	Quickly understand unit and power status with visual indicators.
SmartSlot	Customize UPS capabilities with management cards.
Total Cost of Ownership	
Input power factor correction	Minimizes installation costs by enabling the use of smaller generators and cabling.
Temperature-compensated battery charging	Prolongs battery life by regulating the charge voltage according to battery temperature.
Manual maintenance bypass	Reduces installation costs by eliminating the need for an external mechanical bypass.
Intelligent Battery Management	Maximizes battery performance, life, and reliability through intelligent, precision charging.
Protection	
Frequency and voltage regulation	Gives higher application availability by correcting poor frequency and voltage conditions without using the battery.
Safety-agency	Ensures the product has been tested and approved to work safely with the

approved	connected service provider equipment and within the specified environment. UL, FCC, CE, C-Tick approvals.
Cold-start capable	Provides temporary battery power when the utility power is out.

Output

Output Power Capacity	12 kW / 15 kVA
Max Configurable Power	12 kW / 15 kVA
Nominal Output Voltage	230V,400V 3PH
Output Voltage Note	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Efficiency at Full Load	96%
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal
Crest Factor	Unlimited
Waveform Type	Sine wave
Output Connections	(1) Hard Wire 4-wire (3PH + G) (1) Hard Wire 5-wire (3PH + N + G) (1) Screw Terminals
Bypass	Built-in Maintenance Bypass,Built-in Static Bypass

Input

Nominal Input Voltage	400V 3PH
Input Frequency	47 - 70 Hz (auto sensing)
Input Connections	Hard Wire 5-wire (3PH + N + G)
Input voltage range for main operations	304 - 477V
Other Input Voltages	380,415
Maximum Input Current	21A
Input Breaker Capacity	35A

Batteries & Runtime

Battery Type	VRLA
Included Battery Modules	2
Typical recharge time	5 hour(s)
Replacement Battery	SYBT4
RBC™ Quantity	2
Typical Backup Time at Half Load	27.3 minutes (6000 Watts)
Typical Backup Time at Full Load	9.7 minutes (12000 Watts)

Communications & Management

Interface Port(s)	DB-9 RS-232,Smart-Slot
Pre-Installed SmartSlot™ Cards	AP9619
Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity
Emergency Power Off (EPO)	Yes

Physical

Maximum Height	1499.00 mm
Maximum Width	356.00 mm
Maximum Depth	813.00 mm
Net Weight	396.82 KG
Shipping Weight	428.18 KG
Shipping Height	1643.00 mm
Shipping Width	650.00 mm
Shipping Depth	1062.00 mm
Color	Black
Units per Pallet	1.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0%
Operating Elevation	0-999,9 meters
Storage Temperature	-50 - 40 °C
Storage Relative Humidity	0%
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	64.00 dBA
Online Thermal Dissipation	2170.00 BTU/hr
Protection Class	IP 20

Conformance

Regulatory Approvals	C-tick,CE,EN 50091-2,EN/IEC 62040-3,IEC 61000-3-2,IEC 61000-3-3,ISO 14001,ISO 9001,VFI-SS-112
Standard Warranty	1 year repair or replace,Start-Up Service

**The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.