


**Features:**

- Universal AC input/ Full range
- Built-in active PFC function, PF>0.93
- High Efficiency, and High Reliability
- Wide Operating Ambient Temperature (-20°C~60°C)
- Output Protections: OLP/OVP/SCP
- All using 105°C long life electrolytic capacitors.
- 100% full load burn-in test



Model		QPSF-125-5	QPSF-125-12	QPSF-125-15	QPSF-125-24	QPSF-125-28	QPSF-125-48
Output Characteristics							
DC Output		5V	12V	15V	24V	28V	48V
Rated Current		20A	10.5A	8.4A	5.2A	4.5A	2.6A
Current Range		0~20A	0~10.5A	0~8.4A	0~5.2A	0~4.5A	0~0.42A
Ripple and Noise		100mV	100mV	100mV	100mV	120mV	150mV
Voltage ADJ. Range		±10% of rated output voltage					
Voltage Accuracy		±2.0%	±2.0%	±2.0%	±2.0%	±2.0%	±2.0%
Line Regulation		±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
Load Regulation		±2.0%	±2.0%	±2.0%	±2.0%	±2.0%	±2.0%
Set-up Time		<2500ms (115VAC input, full load); <1200ms (230VAC input, full load)					
Hold-up Time		>17ms (115VAC input, full load); >17ms (230VAC input, full load)					
Temperature Coefficient		±0.03%/°C					
Overshoot and Undershoot		<5.0%					
Input Characteristics							
Voltage Range		90VAC~264VAC					
Frequency Range		47Hz~63Hz					
Power Factor (Typical)		PF>0.98/115VAC PF>0.93/230VAC					
Efficiency (Typical)	115VAC Input	82%	85%	85%	85%	85%	86%
	230VAC Input	84%	87%	87%	87%	87%	88%
AC Current (max)		1.5A	1.5A	1.5A	1.5A	1.5A	1.5A
Inrush Current (Typical)		30A@115VAC Cold start 60A@230VAC Cold start					
Leakage Current		<3.5mA					
Protection							
Over Load (OLP)		105%~150% of rated output current, hiccup mode, auto recover					
Over Voltage (OVP)		120%~150% of rated output voltage, hiccup mode					
Short Circuit (SCP)		Long-term mode, auto recovery					
Environmental Characteristics							
Operating Amb. Temp. & Hum		-20°C~60°C; 20%~90% RH Non-Condensing					
Storage Temp. & Hum		-40°C~85°C: 10%~95% RH Non-Condensing					
Safety Standards		GB4943-2001; EN60950-1: 2006					
Withstand Voltage		Primary-Secondary: 3.0KVAC;≤10mA. Primary-PG: 1.5KVAC;≤10mA. Secondary-PG: 0.5KVDC;≤10mA					
Isolation Resistance		≥100M ohms					
EMI Conduction & Radiation		Compliance to EN55022(CISPR22) Class B					
Harmonic Current		Compliance to EN61000-3-2,-3					
EMS Immunity		Compliance to EN61000-4-2, 3, 4, 5, 6, 8, 11; ENV50204, light industry level, criteria A					
General Characteristics							
MTBF (MIL-HDBK-217F)		More than 100,000Hrs (25°C, Full load)					
Dimension (LxWxH)		127x76x30.5mm					
Packing		21PCS/CTN. G.W: 8.46kgs					
Connection		7P/8.025MM barrier terminal block					
Cooling Method		Cooling by free air convection					

MECHANICAL SPECIFICATIONS



ITEM	CONNECTOR	MATING HOUSING	TERMINAL
AC IN (CON1)	LANDWIN 3961P0300T (CENTER PIN REMOVED)	LANDWIN 3960S OR JST VHR	LANDWIN 3963T011R OR JST SVH-21T-P1.1
DC OUT (CON2)	LANDWIN 3961P0800T		
REMOTE SENSE (CON3)	LANDWIN 2541P0200T	LANDWIN 2510S OR 2540S OR MOLEX 5051	LANDWIN 2563T011X OR 2543T011X OR MOLEX 4809

UNIT: mm