




WIRE READY SPEC. (OPTION -47)
(FOR OPTIONAL SCREW -50
AND STANDARD SCREW.)




NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. INCH DIMENSIONS ARE IN BRACKETS [XXX].
4. REFER TO SD-38120-001 FOR IMPRINTING OPTIONS 10A AND 11A.
5. REFER TO SD-38120-007 FOR IMPRINTING OPTION 12A.
6. *XX* REFERS TO THE QUANTITY OF CIRCUITS.
7. ALL COMPONENTS ARE ROHS COMPLIANT.



4 CIRCUIT SHOWN



NO SCREWS
(OPTION -58 AND -59)
4 CIRCUIT SHOWN

10	XX	#6-32 WRDY W/WASH SCR (-47,-50)	STEEL	ZN, CLEAR CHROMATE
9	XX	#6-32 PH/SLOT WRDY SCR (OPT -47)	STEEL	ZN, CLEAR CHROMATE
8	XX	#6-32 BHD, PH-SL SCREW (OPT -56) C	STAINLESS STEEL	PASSIVATE
7	XX	#6-32 PH/SL W/WASH SCR (-49,-50)	BRASS	NICKEL
6	XX	#6-32 PH/SL W/WASH SCR (OPT -50)	STEEL	ZN, CLEAR CHROMATE
5	XX	#6-32 PH/SLOTTED SCREW (OPT -49)	BRASS	NICKEL
4	XX	#6-32 PH/SLOTTED SCREW (STD)	STEEL	ZN, CLEAR CHROMATE
3	2	MOUNTING PLATE	BRASS	NICKEL
2	XX	TERMINAL	BRASS	BRT.TIN/CU
1	1	INSULATOR, SINGLE ROW	PBT	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

CHG SS SCREW DRIVE RECESS
EC NO: IPG2013-0364
DRAWN: JENC INAS 2012/10/30
CHKD: JMACNEIL 2012/10/30
APPR: JMACNEIL 2012/11/05

QUALITY SYMBOLS	DESCRIPTION
▽=0	
▽=0	


GENERAL TOLERANCES (UNLESS SPECIFIED)	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .01	± .001
2 PLACES	± .02	± .002
1 PLACE	± .03	± .003
ANGULAR	± 2 °	

DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM/IN	2:1	INCH	
DRAWN BY	DATE	TITLE	
W. HOWARD	2003/10/16	9.53MM [.375"] SR BTS, PC ASSY	
CHECKED BY	DATE		
R. KEMP	2003/10/16		
APPROVED BY	DATE		
P. WALTZ	2003/10/16		
MATERIAL NO.	DOCUMENT NO.		

MOLEX INCORPORATED	SHEET NO. 1 OF 2
SEE SHT. 2	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

	10	9	8	7	6	5	4	3	2	1		
	MATERIAL NO. (OPT 12A)	MATERIAL NO. (OPT 11A)	MATERIAL NO. (OPT 10A)	MATERIAL NO. (OPT -59)	MATERIAL NO. (OPT -58)	MATERIAL NO. (OPT -56)	MATERIAL NO. (OPT -50)	MATERIAL NO. (OPT -49,-50)	MATERIAL NO. (OPT -49)	MATERIAL NO. (OPT -47,-50)	MATERIAL NO. (STD)	NUMBER OF CIRCUITS "XX"
F			38729-1039		38729-0750	38729-0659	38729-7402	38729-1381	38729-6802		38729-6201	01
	38729-0872	38729-0025	38729-0014			38729-0791	38729-7403		38729-6803	38729-8603	38729-6202	02
			38729-0940	38729-0945		38729-0117	38729-7404	38729-1159	38729-6804		38729-6203	03
	38729-0256		38729-0940			38729-0839	38729-7404				38729-6204	04
			38729-0346			38729-1253	38729-7405	38729-1382	38729-6805		38729-6205	05
				38729-0400	38729-0386	38729-0980	38729-7406	38729-1383	38729-6806		38729-6206	06
				38729-0423	38729-0407	38729-0435	38729-7406				38729-6207	07
	38729-0497					38729-0440	38729-7407		38729-6807		38729-6207	07
						38729-0508	38729-7408		38729-6808		38729-6208	08
			38729-0548			38729-0532	38729-7409		38729-6809		38729-6209	09
E			38729-1011	38729-0598	38729-0598		38729-7410		38729-6810		38729-6210	10
						38729-1252	38729-7411				38729-6211	11
			38729-0720			38729-0735	38729-7412		38729-6812		38729-6212	12
					38729-0809		38729-7413				38729-6213	13
					38729-0004		38729-7414		38729-6814		38729-6214	14
											38729-6215	15
											38729-6216	16
											38729-6217	17
											38729-6218	18
											38729-6219	19
D											38729-6220	20
											38729-6221	21
											38729-6222	22
											38729-6223	23
											38729-6224	24
											38729-6225	25
											38729-6226	26

	NUMBER OF CIRCUITS "XX"	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"
C	01	30.7 [1.21]	-	19.1 [.75]	11.6 [.46]
	02	40.1 [1.58]	9.53 [.375]	28.6 [1.13]	21.1 [.83]
	03	49.7 [1.96]	19.05 [.750]	38.1 [1.50]	30.6 [1.21]
	04	59.2 [2.33]	28.58 [1.125]	47.6 [1.88]	40.1 [1.58]
	05	68.7 [2.71]	38.10 [1.500]	57.2 [2.25]	49.7 [1.96]
	06	78.2 [3.08]	47.63 [1.875]	66.7 [2.63]	59.2 [2.33]
	07	87.8 [3.46]	57.15 [2.250]	76.2 [3.00]	68.7 [2.71]
	08	97.3 [3.83]	66.68 [2.625]	85.7 [3.38]	78.2 [3.08]
	09	106.8 [4.21]	76.20 [3.000]	95.3 [3.75]	87.8 [3.46]
	10	116.3 [4.58]	85.73 [3.375]	104.8 [4.13]	97.3 [3.83]
B	11	125.9 [4.96]	95.25 [3.750]	114.3 [4.50]	106.8 [4.21]
	12	135.4 [5.33]	104.78 [4.125]	123.8 [4.88]	116.3 [4.58]
	13	144.9 [5.71]	114.30 [4.500]	133.4 [5.25]	125.9 [4.96]
	14	154.4 [6.08]	123.83 [4.875]	142.9 [5.63]	135.4 [5.33]
	15	164.0 [6.46]	133.35 [5.250]	152.4 [6.00]	144.9 [5.71]
	16	173.5 [6.83]	142.88 [5.625]	161.9 [6.38]	154.4 [6.08]
	17	183.0 [7.21]	152.40 [6.000]	171.5 [6.75]	164.0 [6.46]
	18	192.5 [7.58]	161.93 [6.375]	181.0 [7.13]	173.5 [7.21]
	19	202.1 [7.96]	171.45 [6.750]	190.5 [7.50]	183.0 [7.21]
	20	211.6 [8.33]	180.98 [7.125]	200.0 [7.88]	192.5 [7.58]
A	21	221.1 [8.71]	190.50 [7.500]	209.6 [8.25]	202.1 [7.96]
	22	230.6 [9.08]	200.03 [7.875]	219.1 [8.63]	211.6 [8.33]
	23	240.2 [9.46]	209.55 [8.250]	228.6 [9.00]	221.1 [8.71]
	24	249.7 [9.83]	219.08 [8.625]	238.1 [9.38]	230.6 [9.08]
	25	259.2 [10.21]	228.60 [9.000]	247.7 [9.75]	240.2 [9.46]
	26	268.7 [10.58]	238.13 [9.375]	257.2 [10.13]	249.7 [9.83]



PTH PATTERN

SEE SHEET 1 EC NO: PG2013-0364 DRWN: JENC INAS 2012/10/30 CHKD: JMACNEIL 2012/10/30 APPR: JMACNEIL 2012/11/05 REV DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± .01</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.3</td> <td>± ---</td> </tr> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .01	1 PLACE	± 0.3	± ---	DIMENSION STYLE MM/IN DRAWN BY DATE W. HOWARD 2003/10/16 CHECKED BY DATE R. KEMP 2003/10/16 APPROVED BY DATE P. WALTZ 2003/10/16	SCALE 2:1 DESIGN UNITS INCH THIRD ANGLE PROJECTION	TITLE 9.53MM [.375"] SR BTS, PC ASSY
		mm	INCH																	
	4 PLACES	± ---	± ---																	
	3 PLACES	± ---	± .005																	
2 PLACES	± 0.13	± .01																		
1 PLACE	± 0.3	± ---																		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART	DOCUMENT NO. SD-38720-001	SHEET NO. 2 OF 2																
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				