


DRAWING MADE IN THIRD ANGLE PROJECTION		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		, 19					
© COPYRIGHT 19		BY AMP INCORPORATED.		ALL INTERNATIONAL RIGHTS RESERVED.					
PART NO.	A								
863124-1	12.00	[304.8]		OBSOLETE					
863124-2	24.00	[609.6]							
863124-3	36.00	[914.4]		OBSOLETE					
863124-4	60.00	[1524.0]		OBSOLETE					
863124-5	81.00	[2057.4]		OBSOLETE					
863124-6	48.00	[1219.2]							
863124-7	144.00	[3657.6]							
863124-8	240.00	[6096.0]							

LOC	DIST			REVISIONS				
DF	S0	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
					H	REV PER 0H14-0580-04 CT	10-7-04	DE



2.	MARKED PER MIL-STD-130.	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± .01 [0.3] 3 PLC DEC ± - ANGLES ± -	DR 10-7-93 C.C.THOMAS	AMP AMP Incorporated Harrisburg, PA 17105-3608		
3	PIGTAIL IS SOLDER DIPPED.		CHK 10-7-93 D.EABY			
4.	TO MATE WITH AMP LGH-4 RECEPTACLE WITH 2.00 [50.8] BARREL DEPTH.		APPD 10-7-93 D.EABY	NAME LEAD ASSY,SGL. END,SHIELDED.VRL-4,LGH		
5	CUSTOMER TO STRIP AND TERMINATE.		APPD 10-7-93 C.C.THOMAS			
			SEE CALLOUTS	PRODUCT SPEC -		
		FINISH SEE CALLOUTS	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO C-863124
		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	WEIGHT -	SCALE 1:1		SHEET 1 OF 1