

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




NOV ,2005.

© COPYRIGHT 2005 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-05-016219	26NOV05	JMS	FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Ag PLATING
- 4 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 4 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 5000 MOhm
WORKING VOLTAGE: 500 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 1500 Volts RMS Max
CONTACT RESISTANCE: 1.50 mOhm Max
CENTRE CONTACT: 0.20 mOhm Max
VSWR @ xGHz: N/A
INSERTION LOSS xdb: N/A
- 5 MECHANICAL CHARATERISTICS
COUPLING RETENTION FORCE: N/A
CABLE RETENTION FORCE: N/A
DURABILITY: 500 Cycles Min
- 6 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



		1	1	BRASS	3	BODY	4
		1	1	PTFE		INSULATION	3
		1	1	BRASS	3	SLEEVE	2
		1	1	BRASS	3	CONTACT	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 26NOV05	tyco Tyco Electronics Corporation Bideford EX39 4HE						
DIMENSIONS: mm		CHK S.PARLOW 26NOV05	NAME BNC STRAIGHT PCB SOCKET 50 OHM — —						
		APVD F.WHEELER-KING 26NOV05							
		PRODUCT SPEC 108-3435							
		APPLICATION SPEC —							
MATERIAL SEE TABLE		FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1337445	RESTRICTED TO —		
CUSTOMER DRAWING						SCALE NTS	SHEET 1	OF 1	REV C