

## PNP POWER SILICON TRANSISTOR

Qualified per MIL-PRF-19500/441

### DEVICES

2N3740      2N3741

### LEVELS

JAN  
JANTX  
JANTXV  
JANS


### ABSOLUTE MAXIMUM RATINGS ( $T_C = +25^\circ\text{C}$ unless otherwise noted)

| Parameters / Test Conditions                                                                          | Symbol          | 2N3740      | 2N3741 | Unit               |
|-------------------------------------------------------------------------------------------------------|-----------------|-------------|--------|--------------------|
| Collector-Emitter Voltage                                                                             | $V_{CEO}$       | 60          | 80     | Vdc                |
| Collector-Base Voltage                                                                                | $V_{CBO}$       | 60          | 80     | Vdc                |
| Emitter-Base Voltage                                                                                  | $V_{EBO}$       | 7.0         |        | Vdc                |
| Base Current                                                                                          | $I_B$           | 2.0         |        | Adc                |
| Collector Current                                                                                     | $I_C$           | 4.0         |        | Adc                |
| Total Power Dissipation<br>@ $T_A = +25^\circ\text{C}$ <sup>(1)</sup><br>@ $T_C = +100^\circ\text{C}$ | $P_T$           | 25<br>14    |        | W                  |
| Operating & Storage Junction Temperature Range                                                        | $T_J, T_{stg}$  | -65 to +200 |        | $^\circ\text{C}$   |
| Thermal Resistance, Junction-to-Case                                                                  | $R_{\theta JC}$ | 7.0         |        | $^\circ\text{C/W}$ |

**Note:** (1) Derate linearly @ 143 mW/ $^\circ\text{C}$  for  $T_C > +25^\circ\text{C}$

### ELECTRICAL CHARACTERISTICS ( $T_A = +25^\circ\text{C}$ , unless otherwise noted)

| Parameters / Test Conditions                                                                                                           | Symbol        | Min.     | Max.       | Unit             |
|----------------------------------------------------------------------------------------------------------------------------------------|---------------|----------|------------|------------------|
| <b>OFF CHARACTERISTICS</b>                                                                                                             |               |          |            |                  |
| Collector-Emitter Breakdown Voltage<br>$I_C = 100\text{mAdc}$                                                                          | $V_{(BR)CEO}$ | 60<br>80 |            | Vdc              |
| Collector-Emitter Cutoff Current<br>$V_{CE} = 40\text{Vdc}$<br>$V_{CE} = 60\text{Vdc}$                                                 | $I_{CEO}$     |          | 10<br>10   | $\mu\text{Adc}$  |
| Collector-Emitter Cutoff Current<br>$V_{CE} = 60\text{Vdc}, V_{BE} = 1.5\text{Vdc}$<br>$V_{CE} = 80\text{Vdc}, V_{BE} = 1.5\text{Vdc}$ | $I_{CEX}$     |          | 300<br>300 | $\eta\text{Adc}$ |
| Collector-Base Cutoff Current<br>$V_{CB} = 60\text{Vdc}$<br>$V_{CB} = 80\text{Vdc}$                                                    | $I_{CBO}$     |          | 100<br>100 | $\eta\text{Adc}$ |
| Emitter-Base Cutoff Current<br>$V_{EB} = 7.0\text{Vdc}$                                                                                | $I_{EBO}$     |          | 100        | $\eta\text{Adc}$ |



**TO-66 (TO-213AA)**

\* See Appendix A for Package Outline

**ELECTRICAL CHARACTERISTICS ( $T_A = +25^\circ\text{C}$ , unless otherwise noted)**

| Parameters / Test Conditions                                                                                                                                                                                                                                                                | Symbol        | Min.                        | Max.       | Unit |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------------------------|------------|------|
| <b>ON CHARACTERISTICS <sup>(2)</sup></b>                                                                                                                                                                                                                                                    |               |                             |            |      |
| Forward-Current Transfer Ratio<br>$I_C = 100\text{mA}$ , $V_{CE} = 1.0\text{Vdc}$<br>$I_C = 250\text{mA}$ , $V_{CE} = 1.0\text{Vdc}$<br>$I_C = 500\text{mA}$ , $V_{CE} = 1.0\text{Vdc}$<br>$I_C = 1.0\text{A}$ , $V_{CE} = 1.0\text{Vdc}$<br>$I_C = 4.0\text{A}$ , $V_{CE} = 5.0\text{Vdc}$ | $h_{FE}$      | 40<br>30<br>20<br>10<br>3.0 | 120        |      |
| Collector-Emitter Saturation Voltage<br>$I_C = 250\text{mA}$ , $I_B = 25\text{mA}$<br>$I_C = 1.0\text{A}$ , $I_B = 125\text{mA}$                                                                                                                                                            | $V_{CE(sat)}$ |                             | 0.4<br>0.6 | Vdc  |
| Base-Emitter Voltage<br>$I_C = 250\text{mA}$ , $V_{CE} = 1.0\text{Vdc}$                                                                                                                                                                                                                     | $V_{BE(on)}$  |                             | 1.0        | Vdc  |

**DYNAMIC CHARACTERISTICS**

| Parameters / Test Conditions                                                                                                                                  | Symbol     | Min. | Max. | Unit |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|------|------|------|
| Magnitude of Common Emitter Small-Signal Short-Circuit Forward Current Transfer Ratio<br>$I_C = 100\text{mA}$ , $V_{CE} = 10\text{Vdc}$ , $f = 5.0\text{MHz}$ | $ h_{fe} $ | 1.0  | 12   |      |
| Small-Signal Short-Circuit Forward Current Transfer Ratio<br>$I_C = 50\text{mA}$ , $V_{CE} = 10\text{Vdc}$ , $f = 1.0\text{kHz}$                              | $h_{fe}$   | 25   | 250  |      |
| Output Capacitance<br>$V_{CB} = 10\text{Vdc}$ , $I_E = 0$ , $100\text{kHz} \leq f \leq 1.0\text{MHz}$                                                         | $C_{obo}$  |      | 100  | pF   |

**SWITCHING CHARACTERISTICS**


| Parameters / Test Conditions                                                                     | Symbol    | Min. | Max. | Unit          |
|--------------------------------------------------------------------------------------------------|-----------|------|------|---------------|
| Turn-On Time<br>$V_{CC} = 30\text{Vdc}$ ; $I_C = 1.0\text{A}$ ; $I_B = 0.1\text{A}$              | $t_{on}$  |      | 400  | $\mu\text{s}$ |
| Turn-Off Time<br>$V_{CC} = 30\text{Vdc}$ ; $I_C = 1.0\text{A}$ ; $I_{B1} = I_{B2} = 0.1\text{A}$ | $t_{off}$ |      | 1.0  | $\mu\text{s}$ |

**SAFE OPERATING AREA**

|                                                                                                                                                                                                                                                                                                                                       |  |                  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------|
| <b>DC Tests</b><br>$T_C = +25^\circ\text{C}$ , 1 Cycle, $t = 1.0\text{s}$<br><b>Test 1</b><br>$V_{CE} = 6.25\text{Vdc}$ , $I_C = 4.0\text{A}$<br><b>Test 2</b><br>$V_{CE} = 20\text{Vdc}$ , $I_C = 1.25\text{A}$<br><b>Test 3</b><br>$V_{CE} = 50\text{Vdc}$ , $I_C = 150\text{mA}$<br>$V_{CE} = 65\text{Vdc}$ , $I_C = 150\text{mA}$ |  | 2N3740<br>2N3741 |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|------------------|

(2) Pulse Test: Pulse Width =  $300\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$ .

## PACKAGE DIMENSIONS



| Ltr             | Dimensions |      |             |       | Notes   |
|-----------------|------------|------|-------------|-------|---------|
|                 | Inches     |      | Millimeters |       |         |
|                 | Min        | Max  | Min         | Max   |         |
| CD              |            | .620 |             | 15.75 | 9       |
| CH              | .250       | .340 | 6.35        | 8.64  |         |
| HT              | .050       | .075 | 1.27        | 1.91  |         |
| HR              |            | .350 |             | 8.89  |         |
| HR <sub>1</sub> | .115       | .145 | 2.92        | 3.68  | 5       |
| LD              | .028       | .034 | 0.71        | 0.86  | 4, 8, 9 |
| LL              | .360       | .500 | 9.14        | 12.70 | 4, 8    |
| L <sub>1</sub>  |            | .050 |             | 1.27  | 4, 8    |
| MHD             | .142       | .152 | 3.61        | 3.86  | 6, 9    |
| MHS             | .958       | .962 | 24.33       | 24.43 |         |
| PS              | .190       | .210 | 4.83        | 5.33  | 3       |
| PS <sub>1</sub> | .093       | .107 | 2.36        | 2.72  | 3       |
| S               | .570       | .590 | 14.48       | 14.99 | 3       |

### NOTES:

1. Dimensions are in inches.
2. Millimeters are given for general information only.
3. These dimensions should be measured at points .050 to .055 inch (1.27 to 1.40 mm) below seating plane. When gauge is not used, measurement will be made at seating plane.
4. Both terminals.
5. At both ends.
6. Two holes.
7. The collector shall be electrically connected to the case.
8. LD applies between L1 and LL. Lead diameter shall not exceed twice LD within L1.
9. In accordance with ASME Y14.5M, diameters are equivalent to  $\phi$  symbology.
10. Lead 1 is the emitter, lead 2 is the base, collector is the case.

**FIGURE 1.** Physical dimensions, TO-66 (2N3740, 2N3741)