


KBL005 Thru KBL10

4 AMP SILICON BRIDGE RECTIFIER




■ FEATURES

- Rating to 1000V PRV
- Surge overload rating to 200 Amperes peak
- Ideal for printed circuit board
- Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- UL recognized: File #E106441
- UL recognized 94V-O plastic material

■ Mechanical Data

- Case: Molded plastic
- Leads: Silver plated copper
- Leads solderable per MIL-STD-202, Method 208
- Weight: 0.2 ounce, 5.6 grams

■ Outline Drawing



■ Maximum Ratings & Characteristics

- Ratings at 25° C ambient temperature unless otherwise specified
- Single phase, half wave, 60Hz, resistive or inductive load
- For capacitive load, derate current by 20%

		KBL005	KBL01	KBL02	KBL04	KBL06	KBL08	KBL10	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	60	100	200	400	600	800	1000	V
Maximum Average Forward Output Current @ $T_A = 50^\circ C$	$I_{(AV)}$				4.0				A
Peak Forward Surge Current 8.3 ms Single Half-Sine-Wave Superimposed On Rated Load	I_{FSM}				200				A
Maximum DC Forward Voltage Drop per Element At 3.0A DC	V_F				1.1				V
Maximum DC Reverse Current At Rated @ $T_A = 25^\circ C$ DC Blocking Voltage per Element @ $T_C = 100^\circ C$	I_R				10				μA
I^2t Rating for Fusing ($t < 8.3ms$)	I^2t				1	166			$A^2 S$
Operating Temperature Range	T_J				-55 to +125				°C
Storage Temperature Range	T_{STG}				-55 to +150				°C