




PRODUCT NO.
52486-050HA/050HALF



NOTES:

- 8mm MIN. CARD EJECT.
 - EJECT TRAVEL: 9.5mm
 - MATERIAL
 - HEADER ASS'Y
 - PLASTIC : HOUSING ...LCP UL94V-0 BLACK
 - PIN : COPPER ALLOY
 - PCB : FR4
 - EJECT MECHANISM ASS'Y
 - PLASTIC : GUIDE: POLYPHTHARAMID UL94V-0 BLACK
 - BUTTON: POLYPHTHARAMID UL94V-0 BLACK
 - PLATE : STAINLESS
 - EMI CONTACT: PHOSPHOR BRONZE
 - RECEPTACLE
 - PLASTIC : LCP 94V-0, NATURAL.
 - PIN: BeCu
 - FINISH (PIN)
 - UNDER PLATING : 0.5 um MIN. Ni
 - CONTACT AREA : 0.1 um MIN. GOLD OVER
 - 0.5 um MIN. Pd-Ni
 - SOLDER TAIL : 2.5 um MIN. Sn-Pb
 - 2.5 um MIN. PURE Sn (FOR -050HALF)
 - PUSH ROD LOCATION AND P.C.B. SIDE ARE AS APPEARS INSTALLED.
 - DIM "X"
- | | | |
|----------|---------|------------------|
| 4.25±0.1 | 3.5±0.1 | 5.0±0.1 |
| OTHERS | 36,67 | 1,17,34,35,51,68 |
- P.C.B LAYOUT REFERED TO TA-1052.
 - IF LEAD FREE P/N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
 - LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - IF LEAD FREE P/N. PACKAGING MEETS GS-14-920 SPECIFICATION

ORDERING INFORMATION

NAME	PART NO.	Q'TY
Ⓐ EJECT HEADER ASS'Y	52486-050HA/050HALF	1
Ⓑ MATING RECEPTACLE	91931-31169/31169LF	1

mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS			
rev.	ecn no.	dr	date	linear	± 0.30	projection		title			
A	T90421	M	W12/17/99					EJECTOR HEADER ASS'Y			
B	T20085	WL	03/18/02					68POS. FOR TYP 1/2/3			
C	N05-0128	WB	05/20/05	angles	± 2°						
		dr	WENDY CHEN	08/30/99	unit			product family : PCMCIA		code	
		enrg	STELAR CHU	08/30/99	mm/inch			size		TWN	
		chr	JOSEPH HSIA	08/30/99	scale			dwg no.		sheet	
		appd	LELAND WANG	08/30/99	1.2:1			A3		1 OF 1	
sheet	revision	C									
index	sheet	1									