




PART NUMBER	10089865-10XLF
-------------	----------------

NO.	COMPONENT NAME	CABLE VERSION:				Q'TY
		6mm <sup>2</sup> - 4mm <sup>2</sup>	4mm <sup>2</sup> - 2mm <sup>2</sup>	6mm <sup>2</sup> - 4mm <sup>2</sup>	4mm <sup>2</sup> - 2mm <sup>2</sup>	
6	JUMPER CONTACT	<input type="circle"/>	<input type="circle"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	1
5	FRONT HOUSING	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	<input type="checkbox"/>	1
4	RECEPTACLE CONTACT	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	<input type="checkbox"/>	2
3	SCREW	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	<input type="checkbox"/>	1
2	BOTTOM COVER	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	<input type="checkbox"/>	1
1	TOP COVER ASSEMBLY	LATCH SLIDE	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	1
		NUT HEXAGON	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	1
		TOP COVER	<input type="circle"/>	<input type="circle"/>	<input type="checkbox"/>	1

" " if used, or "X" if not used.



RECOMMENDED CABLE SPECIFICATION	
6mm <sup>2</sup> - 4mm <sup>2</sup>	4mm <sup>2</sup> - 2mm <sup>2</sup>
10 - 12 AWG	12 - 14 AWG

spec ref	-		dr	J. DE BRUIJN	2008-08-05	projection	mm	size	scale	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	NICK ZHANG	2016-11-18	product family	← →	ecn no	ELX-N-25383	
ISO 406			chr	NICK ZHANG	2016-11-18					
ISO 1101			appr	TIM YAO	2016-11-18					
ISO 1302	surface	linear	0.X	±0.3	Amphenol FCi	STRAIGHT CC ASSEMBLY KIT		dwg no	rev	
		0.XX	±0.15	Power Profile Plus, Cable Conn.						
		0.XXX	±0.05			cat. no.		10089865	E	
	angular	0°	±2°			Product - Customer Drw				

