

Coaxial

Power Splitter/Combiner

ZMSC-3-1

3 Way-0° 50Ω 1 to 200 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.375W max.

Coaxial Connections

SUMPORT	S
PORT 1	1
PORT 2	2
PORT 3	3

Outline Drawing



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	
1.50	1.13	1.00	.50	.155	2.345	.138	.987	
38.10	28.70	25.40	12.70	3.94	59.56	3.51	25.07	
J	K	L	M	N	P	Q	S	wt
2.50	.10	.50	1.00	--	.31	.81	.150	grams
63.50	2.54	12.70	25.40	--	7.87	20.57	3.81	42.5

Features

- low insertion, 0.4 dB typ.
- high isolation, 40 dB typ.
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 1 deg. typ.
- excellent VSWR, 1.1:1 typ.
- rugged shielded case

Applications

- VHF
- instrumentation
- radio communication system



CASE STYLE: P26




Connectors	Model	Price	Qty.
SMA	ZMSC-3-1	\$57.95	(1-9)
BRACKET (OPTION "B")		\$5.00	(1+)
BRACKET (OPTION "BR")		\$1.50	(1+)

Splitter Electrical Specifications


FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 4.8 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
f_L - f_U	Typ.	Min	Typ.	Max.	Max.	Max.
1-200	40	25	0.4	0.7	2	0.2

Typical Performance Data

Freq. (MHz)	Insertion Loss (dB)			Amp. Unbal. (dB)	Isolation (dB)			Phase Unbal. (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3
	S-1	S-2	S-3		1-2	1-3	2-3					
1.00	5.09	5.09	5.10	0.01	46.35	47.66	41.10	0.06	1.11	1.09	1.09	1.09
4.00	5.02	5.02	5.02	0.01	45.95	46.40	38.74	0.07	1.06	1.04	1.03	1.04
8.00	5.03	5.04	5.03	0.01	44.98	45.00	37.47	0.09	1.04	1.02	1.02	1.02
26.00	5.06	5.06	5.06	0.00	41.67	42.34	36.29	0.19	1.03	1.02	1.02	1.02
50.00	5.08	5.08	5.08	0.00	38.76	40.53	35.80	0.43	1.04	1.02	1.02	1.02
65.00	5.10	5.10	5.11	0.01	37.43	39.67	35.68	0.53	1.05	1.03	1.02	1.02
80.00	5.10	5.11	5.12	0.02	36.35	38.96	35.64	0.64	1.05	1.03	1.02	1.02
95.00	5.13	5.13	5.14	0.01	35.50	38.55	35.78	0.79	1.06	1.04	1.02	1.02
110.00	5.15	5.14	5.16	0.02	34.89	38.39	36.01	0.90	1.06	1.04	1.02	1.02
125.00	5.16	5.15	5.18	0.02	34.50	38.52	36.51	0.95	1.07	1.04	1.02	1.02
140.00	5.16	5.16	5.18	0.03	34.28	38.84	37.29	1.08	1.07	1.05	1.02	1.02
160.00	5.17	5.17	5.21	0.04	34.27	39.90	38.89	1.17	1.08	1.05	1.02	1.02
175.00	5.18	5.20	5.23	0.05	34.50	41.29	40.75	1.29	1.08	1.05	1.02	1.02
185.00	5.19	5.21	5.25	0.06	34.78	42.35	42.20	1.31	1.09	1.05	1.02	1.02
200.00	5.23	5.24	5.29	0.06	35.36	43.22	43.31	1.48	1.10	1.05	1.01	1.02



electrical schematic



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

REV. OR
M94793
ZMSC-3-1
HY/TD/CP
060905