









- CODINGS
Kodierungen
1:1




Kupplung COUPLING	0.0005	E	5-1418639-5	B	PBT-GF10	maigrün / MAY GREEN äehn. / sim. RAL 6017
	0.0005	B	2-1418639-5	B		natur / NATURE
	0.0005	A	1-1418639-5	B		schwarz / BLACK äehn. / sim. RAL 9011
TITLE Benennung	Masse (kg) MASS (kg)	COO	TE- Bestell-Nr. ORDER-Nr.	REV	Werkstoff MATERIAL	Oberflaeche/Farbe SURFACE/CLOUR

SOCKET HOUSING
IN END LOCKED POSITION
Buchsengehäuse
in Endraststellung



TAKE OFF THE HOUSING
WITH SCREWDRIVER ONLY
(E.G. WITH SIZE 50 x 2.5mm)
Endriegelung des Gehäuses
nur mit Schraubendreher
(z.B. Grösse 50 x 2.5mm)



TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-10 (ENTRICK TO NOMINAL DIMENSION, EDITION 1982-11) SHALL APPLY. Fertigungstoleranzen nach DIN 16901-10, Es gilt die Ausgabe 1982-11.		DWN 06MAR2007 R. Bachmann		lyco Electronics AMP GmbH D - 64625 Bensheim	
THIS DRAWING IS A CONTROL COPY FOR THE ELECTRONICS CORPORATION THIS DRAWING IS THE PROPERTY OF THE ELECTRONICS CORPORATION THIS DRAWING IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER THIS DRAWING IS NOT TO BE LOANED, REPRODUCED OR COPIED IN ANY MANNER THIS DRAWING IS NOT TO BE REPRODUCED OR COPIED IN ANY MANNER		CWH 07MAR2007 H. Holland-Cun		NAME	
DIMENSIONS: MASS IN mm		APVD 07MAR2007 J. Woller		SOCKET HOUSING, 2POS., MQS Buchsengehäuse, 2polig, MQS	
		PRODUKT SPEC PRODUKT SPEC 108-18620-1		SIZE CASE CODE DRAWING NO ZEICHNUNG-NR. A 1 00779 C-148639	
MATERIAL FINISH ANGLE(S) OF FINISH FINISH		WEIGHT GEWICHT		RESTRICTED TO NUR FÜR -	
CUSTOMER DRAWING		/KUNDENZEICHNUNG		SCALE MASSSTAB 5:1 SHEET BLATT 1 OF 1 REV B	