

PRODUCT NUMBER
98423-XXX-XXXLF

PLATING

S = 0.38µm GOLD/GXT
ON CONTACT AREA
2µm MIN MATTE
TIN ON TAIL

G = 0.76µm GOLD/GXT
ON CONTACT AREA
2µm MIN MATTE
TIN ON TAIL

F = GOLD FASH
ON CONTACT AREA
2µm MIN MATTE

RoHS COMPATIBLE, SEE NOTE 6

PACKAGING OPTIONAL LETTER (SEE NOTE 5)

NB OF POSITIONS PER ROW
02 TO 25 POS

PIN STYLE	MATING STYLE	SOLDER STYLE
61	4.00	2.50
62	7.00	3.00
63	7.00	3.50

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR BLACK
2. MATERIAL TERMINAL: COPPER ALLOY
3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING:
= PLASTIC BOX
U = TUBE AVAILABLE FROM 06 TO 50 POS

6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:





- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920
- THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 101		projection 		product family MINITEK			
ltr	ecn no	dr	date	tolerances unless otherwise specified				 mm scale 1:1	title UNSHR HEADER RIGHT ANGLE TMT				
A	F10338	LMU	03.10.01	angles	linear	X ±0.3							
B	F04-0351	JCO	05.01.13			X.X ±0.13							
C	F06-0210	LMU	06.07.05			X.XX ±0.05							
D	F08-0145	ELA	17.04.08	dr	L MULIN	04.09.28							
E	B-19190	LMU	14.10.24	engr	J COMPAGNON	04.09.28							
F	F-25393	DDE	16.11.21	chr									
G	F-26943	DDE	17.05.10	appd	JM.C	04.09.28							
sheet index	revision sheet								dwg no 98423		sheet 1 of 1 A3		
									type CUSTOMER Drawing				