

# Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

**BELDEN**  
SENDING ALL THE RIGHT SIGNALS

**1530A Coax - CATV Cable**



For more Information  
please call

1-800-Belden1



## General Description:

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II + aluminum braid shield (90% coverage), PVC jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCCS - Bare Copper Covered Steel	.040

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.180

### Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	90

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

## Overall Cable

Overall Nominal Diameter: 0.270 in.

## Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 28 lbs/1000 ft.

Max. Recommended Pulling Tension: 162 lbs.

Min. Bend Radius/Minor Axis: 2.750 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CATV, CM

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (RoHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Series Type: Series 6

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

## 1530A Coax - CATV Cable

### Flame Test

UL Flame Test: UL1685 UL Loading

### Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1530AP

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)  
75.000

#### Nom. Inductance:

Inductance (pH/ft)  
.097

#### Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)  
16.2

#### Nominal Velocity of Propagation:

VP (%)  
83

#### Nominal Delay:

Delay (ns/ft)  
1.2

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)  
28.0

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)  
5

#### Max. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
5	0.67
55	1.60
211	2.87
270	3.24
300	3.43
350	3.72
400	4.00
450	4.26
550	4.71
750	5.59
870	6.00
1000	6.54

#### Max. Operating Voltage - UL:

Voltage  
350 V RMS

#### Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
	5	1000	20	

### Sweep Test

Sweep Testing: 5 MHz - 1 GHz

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1530A Q5HU1000	1,000 FT	30.000 LB	WHITE, NEUTRAL		#18 GIFTLDPE SH FR PVC
1530A Q5H1000	1,000 FT	31.000 LB	WHITE, NEUTRAL		#18 GIFTLDPE SH FR PVC
1530A O10U1000	1,000 FT	30.000 LB	BLACK		#18 GIFTLDPE SH FR PVC
1530A O101000	1,000 FT	31.000 LB	BLACK		#18 GIFTLDPE SH FR PVC

# Detailed Specifications & Technical Data



## ENGLISH MEASUREMENT VERSION

### 1530A Coax - CATV Cable

Revision Number: 2 Revision Date: 08-10-2012

© 2014 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1530A 010U1000](#) [1530A 0101000](#)