

## 1283S6 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles



For more Information  
please call

1-800-Belden1



### General Description:

20 AWG solid .032" bare copper conductors, foam FEP insulation, Duofoil® + tinned copper braid shield (95% coverage), Flamarrest® jackets in colors, center spline binder.

### Usage (Overall)

**Suitable Applications:** RGB, VGA, SVGA, XGA, SXGA, UXGA, HDTV, LCD, Plasma, Digital Signage, Component Video, Video Mult, Animation, Special effects. Suitable for use in Plenum spaces

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
6	20	Solid	BC - Bare Copper	0.8128

**Total Number of Conductors:** 6

#### Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FFEP - Foam Fluorinated Ethylene Propylene	3.3782

#### Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

#### Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
Plenum Grade PVC - Polyvinyl Chloride	4.9784

Inner Jacket Color Code Chart:

Number	Color
1	Red
2	Green
3	Blue
4	White
5	Yellow
6	Brown

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

#### Overall Cable

**Overall Cabling Fillers:** Bonded Spline

**Overall Nominal Diameter:** 14.935 mm

### Mechanical Characteristics (Overall)

**Operating Temperature Range:** -20°C To +75°C

**UL Temperature Rating:** 60°C

**Non-UL Temperature Rating:** 75°C

**Bulk Cable Weight:** 291.687 Kg/Km

## 1283S6 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles

Max. Recommended Pulling Tension:	960.811 N
Min. Bend Radius/Minor Axis:	165.100 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	06/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

#### Applicable Patents:

Country
www.belden.com/p

#### Flame Test

UL Flame Test:	NFPA 262
----------------	----------

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

#### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)
75

#### Nom. Inductance:

Inductance (µH/m)
0.351067

#### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
53.1522

#### Nominal Velocity of Propagation:

VP (%)
83

#### Nominal Delay:

Delay (ns/m)
4.00282

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
32.81

#### Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)
12.4678

#### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	0.9843
3.6	1.9686
10	2.9529
71.5	6.8901
135	8.8587
270	12.4678
360	14.4364

## METRIC MEASUREMENT VERSION

### 1283S6 Coax - Banana Peel® Unjacketed VideoFLEX® Bundles

540	18.0455
720	20.9984
750	21.3265
1000	24.9356
1500	30.8414
2500	40.6844
3000	45.2778

#### Max. Operating Voltage - UL:

<b>Voltage</b>
300 V RMS

**Other Electrical Characteristic 1:** Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination.

**Other Electrical Characteristic 2:** Return Loss Tested in Accordance With ASTM D-4566 Paragraph 45.3, Using a 75 Ohm Fixed Bridge and Termination.

#### Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	850	23
851	3000	15

#### Sweep Test

**Sweep Testing:** Sweep tested 5 MHz to 3 GHz.

#### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1283S6 0001000	1,000 FT	209.000 LB	NONE	C	6C20 RGBHVC
1283S6 000250	250 FT	59.000 LB	NONE	C	6C20 RGBHVC
1283S6 000500	500 FT	108.000 LB	NONE	C	6C20 RGBHVC

**Notes:**  
C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 11-01-2013

© 2015 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.