



FTA040 Series

40 W ITE Open Frame Power Supply

- High Efficiency: Level V
- Fully Regulated DC Output
- Lifetime Expectation >5 years
- Hold-up Time >14ms at full load
- EISA Compliant
- CEC Compliant
- Grounded Output
- Safety Approval - EN60950-1

Elpac Part Number	Output Voltage	Output Current	Peak Current	Total Regulation	Typical Efficiency
FTA040009A	9.0V	4.4A	5.3A	±5%	85%
FTA040012A	12.0V	3.3A	4.0A	±5%	87%
FTA040015A	15.0V	2.7A	3.2A	±5%	88%
FTA040024A	24.0V	1.7A	1.6A	±5%	87%

Input

Input Voltage	85 - 264VAC 100 - 240VAC Nominal
Input Frequency	47 - 63Hz
Input Current	<1.0A rms
Inrush Current	<37A at 230VAC cold start
Zero Load Power Consumption	<0.3W
Touch Leakage Current	<60µA @ 132VAC @ 60Hz <80µA @ 264VAC @ 60Hz

Output

Output Voltage	See Table
----------------	-----------

Total Regulation	+/-5%
Minimum Load	No minimum load required
Start-Up Delay	<250ms
Hold-Up Time	>14ms
Ripple & Noise	<1% pk-pk **
Over Voltage Protection	110-135%
Over Temperature Protection	Active - Recoverable; plus Passive - Non Recoverable
Over Current Protection	120 - 180%
Short Circuit Protection	shutdown, auto-restart (hiccup mode)

General

Efficiency	Avg Efficiency 87.1% @ 115VAC; 87.1% @ 230VAC
MTBF	min. 200,000 hours demonstrated
Size	4.00
Weight	0.29 lbs (0.13 kg)
Power Density	5.76W/in ³

Environmental

Operating Temperature	0 – 70°C (Full load to 50°C, derate linearly to 50% load at 70°C)
Storage Temperature	-40°C to +85°C
Relative Humidity	5-95%, non-condensing
Cooling	Natural Convection
Vibration	All units production tested to 19.6m/s ²

EMC & Safety

Emissions	FCC class B, CISPR22 class B EN61000-3-2, -3
Immunity	EN61000-4-2, -3, -4, -5, -6, -8, -11
Certified by TUV to the following:	cTUVus UL 60950-1 CAN/CSA-22.2 No.60950-1



	CB per IEC60950-1
	CE marked to LVD