


21.4MHz

CERAMIC SURFACE-MOUNT MONOLITHIC CRYSTAL FILTERS

ASCF21U Series



FEATURES:


- Surface-Mount ceramic package.
- Excellent attenuation Bandwidth.
- Reflow capable.
- Low height (1.5mm max.).

APPLICATIONS:

- Mobile Communication Systems.
- Cellular & Cordless Phones.
- Pagers.
- Radios.

STANDARD SPECIFICATIONS

ABRACON PIN NO.	POLE	PASSBAND		STOPBAND		RIPPLE dB	LOSS dB	TERMINATING IMPEDANCE (Ω // pF)
		dB	kHz	dB	kHz			
ASCF21U8	2	3	± 3.75	20	± 18.0	1.0	2.0	(850 // 5.0)
ASCF21U15	2	3	± 7.50	18	± 25.0	1.0	2.0	(1500 // 1.0)
ASCF21U20	2	3	± 10.00	10	± 30.0	1.0	2.0	(1800 // 1.0)
ASCF21U30	2	3	± 15.00	15	± 45.0	1.0	2.0	(2000 // 1.5)



Environmental and mechanical specifications, Group 2.

We Manufacture to your Custom Specifications. Please Call for Details

Operating Temperature: -20°C to + 70°C.

PIN CONNECTIONS

PIN	FUNCTION
1	IN
2	GND
3	GND
4	OUT
5	GND
6	GND

Dimensions: Inches (mm)

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED

NOTE: Left blank if standard • All specifications and markings subject to change without notice

29 Journey • Aliso Viejo, CA 92656 • USA
(949) 448-7070 • FAX: (949) 448-8484

E-MAIL: abinfo@abracon.com • INTERNET ADDRESS: www.abracon.com

ABRACON[®]
CORPORATION