

TM-17B TM-17SS / TM-17SUS Brass Sheet Chain





Characteristic

Select one from stainless steel, brass, or steel made chains depending on your application.

Application

Machine tools / Office utilities / Farm machines, etc.



Model No.	Material	Finish
TM-17B	BSP	—
TM-17SS	SPCC	Uc
TM-17SUS	SUS304	—

TM-17B

Model No.	A	B	C	Breaking Load kN (kgf)	Net Weight (g/30m Standard Length)	Code No.
TM-17B-15	9.5	4	t0.3	0.15 (15)	350	5876
TM-17B-16	11	4.8	t0.4	0.29 (30)	560	5877
TM-17B-B-18	15	4.9	t0.3	0.20 (20)	380	5878
TM-17B-18	5	t0.4	0.29 (30)	580	5879	
TM-17B-19	17.5	5.5	t0.5	0.49 (50)	880	5880
TM-17B-20	18	6.3	t0.7	0.88 (90)	1430	5881
TM-17B-22	17	8	t0.8	0.98 (100)	2100	5882
TM-17B-23	20.5	9.5	t1.2	1.96 (200)	3400	5883
TM-17B-24	24	12	t1.5	2.94 (300)	6000	5884

TM-17SS

Model No.	A	B	C	Breaking Load kN (kgf)	Net Weight (g/30m Standard Length)	Code No.
TM-17SS-19	17.5	5.5	t0.5	0.49 (50)	880	5885
TM-17SS-20	18	6.3	t0.7	0.98 (100)	1400	5886
TM-17SS-22	17	8	t0.8	1.28 (130)	1900	5887
TM-17SS-23	20.5	9.5	t1.2	1.96 (200)	3100	5888
TM-17SS-24	24	12	t1.5	3.43 (350)	6200	5889

TM-17SUS

Model No.	A	B	C	Breaking Load kN (kgf)	Net Weight (g/30m Standard Length)	Code No.
TM-17SUS-18	15	5	t0.4	0.69 (70)	500	5890
TM-17SUS-19	17.5	5.5	t0.5	0.98 (100)	900	5891
TM-17SUS-20	18	6.3	t0.7	1.96 (200)	1200	5892

※If you need the chain cut or assembled, please contact us about the price and delivery date.

TM-177 Ball Chain Assembly



Characteristic


Excellent performance on corrosion-resistance and heat-resistance. Length can be specified when ordering.

(Custom made product.)

※Contact us about the delivery date, since it is a custom made product.

Application

Office utilities / Home Appliances / Lighting devices / Medical instruments



Model No.	Breaking Load N (kgf)	Code No.
TM-177	98.1 (10)	5945

Model No.	Net Weight /50m Standard Length	Code No.
Chain		5947
Terminal	0.8g	5946

Parts List

No.	Part Name	Material	Finish	Quantity
1	Terminal	SUS304	—	2
2	Ball	SUS305	Electrolytic Polishing	—
3	Joint			—