

4

3




2

1


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1							
			C 1	ECR-10-023156	11NOV2010	SR	OH

PN 0-1 As Shown

Contact arrangement
view from connecting side




Contact arrangement
view from termination side



NOTES

- SUITABLE CRIMP CONTACTS: SERIES HSK
CUSTOMER DRAWING: 1108757
OUTER DIMENSIONS OF INSULATION: MAX. Ø8mm
- SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250
- SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
- SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
-  POLARIZATION RIBS
-  MARKING OF POLARIZATION ACCORDING TO MARKING OF
MODULE FRAME
- PACKAGING:
10 PIECES IN A CARTON


PN 0-1 As Shown



1	FEMALE INSERT	PC-GF20	LYGHT GREY	1
0-1	DESCRIPTION	MATERIAL	COLOR	ITEM NO
HVS-HSK.3.Sti.C				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		ISO 8075 DIN 150 2768 mH-E DIN 16901-120	
	0 PLC	±	
	1 PLC	±	
	2 PLC	±	
	3 PLC	±	
	4 PLC	±	
MATERIAL		FINISH	
			

DWN	20.02.2006
CHK	20.02.2006
APVD	20.02.2006
PRODUCT SPEC	108-74081
APPLICATION SPEC	114-74083
WEIGHT	
CUSTOMER DRAWING	

 Tyco Electronics		Tyco Electronics AMP GmbH 53757 Sankt Augustin, Germany	
NAME MALE INSERT HVS-HSK.3.STI.C			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A 3	00779	C=1103272	
SCALE		SHEET	OF
2:1		1	1
		REV	1