
B





PTS645 Series 6 mm Tact Switches

SERIES 

PTS645




PTS645S Model




PTS645V Model

TERMINATION 


S STRAIGHT




PCB LAYOUT




T STRAIGHT WITH ESD PIN




PCB LAYOUT





V VERTICAL



PCB LAYOUT



SMT



Dimensions are shown: mm (inches)
Specifications and dimensions subject to change

PTS645 Series 6 mm Tact Switches

ACTUATION FORCE




OPTION CODE	FORCE
L	130 grams
M	160 grams
H	200 grams
K	260 grams

ACTUATOR HEIGHT




OPTION CODE	HEIGHT "H" or LENGTH "L"	TERMINATION	SCHEMATIC	
			Without EMC pin	With EMC pin
43	4,3 (.169)	Thru-hole and SMT		
50	5,0 (.197)	Thru-hole and SMT		
70	7,0 (.275)	Thru-hole		
95	9,5 (.374)	Thru-hole		
31	3,15 (.124)	Vertical		
39	3,85 (.151)	Vertical		
58	5,85 (.230)	Vertical		
83	8,35 (.329)	Vertical		
15	15,85 (.624)	Vertical		


43




50




70




95




31




39




58



83



15



First Angle
Projection

