

10072353-X01-XXXL

S = 0.38μm GOLD/GXT ON CONTACT AREA
2.0μm MIN MATTE TIN ON TAIL

ROHS COMPATIBLE
NOTE 6


G = 0.76μm GOLD/GXT ON CONTACT AREA
2.0μm MIN MATTE TIN ON TAIL

PACKAGING NOTE 5

F = GOLD FLASH ON CONTACT AREA
2.0 μ m MIN MATTE TIN ON TAIL

NB OF POSITIONS PER ROW
02 TO 25 PDS

1.27 μm MIN NICKEL UNDERPLATING



1. MATERIAL HOUSING: HIGH TEMP, THERMOPLASTIC
UL 94V-0, COLOR BLACK

2. MATERIAL TERMINAL: COPPER ALLOY

3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW.

4. 7N MIN PIN RETENTION IN EITHER DIRECTION.

5. PACKAGING :

= PLASTIC BOX

U = TUBE AVAILABLE FROM 06 TO 50 PDS
6. ROHS COMPATIBLE PRODUCT SPECIFICATIONS

α - PLATING

= "LF" MEANS THE PRODUCT IS LEAD-FREE
2µm MINIMUM MATTE TIN OVER 127µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INRA-RED DR VAPOR PHASE OR REFLOW OVEN.

C - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920.

d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004

rev	ecn no	dr	date
A	F06-0326	LMU	07.01.04
B	F08-0145	ELA	17.04.08
C	B-19190	LMU	14.10.24
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface -		tolerance std		projection		mm	
		ISO 1302		ISO 406 ISO 1101				↔	
		TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	L MULIN	ANGULAR				size		Scale	
Eng	J COMPAGNON	LINEAR		0.X ± 0.13		A3		5:1	
Chr	-	0° ±2°		0.XXX ± 0.05		ECN		-	
Appr	JMC	06.09.14		Product family		Mintek		Spec ref	
UNSHR HEADER		RIGHT ANGLE PIP		O.D		10072353		Rev.	
catalog no		-		CUSTOMER Drawing		sheet 1 of 1		C	

