







RECOMMENDED P.C.B. LAYOUT



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.25 ± 0.1 mm
6. OPERATING FORCE: 160 ± 50 gf
7. CONTACT RESISTANCE: 100 milliohms Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.
9. DESIGNATE MAJOR DIMENSIONS
10. MATERIAL: PPS (STEM & BODY) TO WITHSTAND
IR REFLOW TEMP. OF 260°C MAX. FOR 30 SECONDS



TITLE				E-SWITCH®			
C	11844	ADD	TEMPERATURE NOTE	11/28/01	CJB	SCALE	4:1
REV.	ECN No.	DESCRIPTION	DATE	CHKD	DATE	DR	CJB
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND ITS NOT TO BE COPIED OR TRANSFERRED				P020230			
				REV C			