


CARLO GAVAZZI
Automation Components

Relays



Switch





Monostable or Bistable Miniature Power Relays

CARLO GAVAZZI



- Miniature size 15 mm high
- PCB mounting
- Monostable or bistable versions
- 4 kV / 8 mm insulation
- Switching capacity 8 A / 250 VAC
- DC coils:
 - 2 to 147 VDC monostable version
 - 2.4 to 84.7 VDC bistable version
- 1 normally open contact or
1 change over contact
- General purpose, industrial electronics
- Sealed according to IP 67 standard
- 4 different pin layout configuration
- Low coil power consumption

Type **M15**




- Miniature size 15.7 mm high
- PCB mounting
- Monostable version
- 5 kV / 10 mm insulation
- Switching capacity:
 - 12 or 16 A / 250 VAC 1 pole version
 - 8 A / 250 VAC 2 pole version
- DC coils 5 to 110 VDC
- 1 or 2 change over contacts
- General purpose, industrial electronics
- Sealed according to IP 67 standard
- Low coil power consumption

Type **M25**




To instantly view a data sheet and specify products, visit www.GavazziOnline.com

Relay



TYPE	M15 - M15 R1/R2	M25	RMI 2-10 / RMI 4-5	RCP
DIMENSIONS				
Height - Length - Width	15 x 29 x 10	15.7 x 29 x 12.7	36 x 28 x 21.5	56 x 35.5 x 35.5
CONTACTS				
Configuration	1 CO, 1 NA	1 CO, 2 CO	2 CO, 4 CO	2 CO, 3 CO
Material	AgCdO	AgCdO	Silver alloy	Silver alloy
Rated current	8 A	8 A, 12 A, 16 A	5 A, 10 A	10 A
Max. switching power	2000 VA	2000VA-3000VA-4000VA	300 W-2500 VA (2 poles) 150 W-1250 VA (4 poles)	300 W- 2500 VA
	-	-	250 VAC / 30 VDC	-
Max. contact voltage	380 VAC	440 VAC		380 VAC
Minimum permissible load (Typical value)	100 mA at 24 VDC 10 mA at 10 mVDC (Au)	100 mA at 24 VDC -	- -	100 mA at 24 VDC -
COIL				
Rated voltage	DC	5 to 110 VDC	5 to 110 VDC	6 to 110 VDC
		3 to 48 VDC (M15 R1) 3 to 24 VDC (M15 R2)	- -	- -
	AC	-	6 to 230 VAC	6 to 230 VDC
Consumption	DC	100 mW V_{min}	0.9 W	1.3 W
	AC	-	1.9 VA	2.1 VA
Operating range		0.7 to 1.7 Vn	0.7 to 1.7 Vn	-
GENERAL DATA				
Electrical life (at max. switching power)	1 x 10 ⁵ cycles	1 x 10 ⁵ cycles	1 x 10 ⁵ ops (1800 ops/h)	1 x 10 ⁵
Mechanical life	30 x 10 ⁶ cycles	1 x 10 ⁷ cycles	1 x 10 ⁷ ops (18000 ops/h)	1 x 10 ⁷
Insulation test VAC (1min)				
- Contact/coil	4000 VAC	5000 VAC	3750 VAC Vrms	3750 VAC Vrms
- Open contacts	1000 VAC	1000 VAC	750 VAC Vrms	750 VAC Vrms
- Contact different polarity	-	2500 VAC (1 pole)	1250 VAC Vrms	1250 VAC Vrms
Protection category		IP 67	IP 67	IP 40 IP 40
Operating temperature	-40°C to +70°C	-40°C to +85°C	-55°C to +70°C	-40°C to +55°C
Terminal shape	PCB	PCB	Plug-in and PCB	Plug-in
Approvals	UL, CSA, VDE, IMQ S, N, D, F	VDE	UL, CSA, VDE, IMQ	UL, CSA, VDE, IMQ
OPTIONS				
	AgNi, AgSnO ₂ Gold plated contacts	AgNi, AgSnO ₂ Gold plated contacts	-	-
SOCKETS				
	LED Indication	Diode Protection	RC Network Protection	MOV Protection



CARLO GAVAZZI offers a wide range of **printed circuit board and modular DIN rail mount sockets** for our various electromechanical relays. The following optional plug-in blocks are also offered for the DIN rail mount sockets:

Ordering Key				Pin Layout Configuration	Contact Material	Version	Contact Code	Contact Rated Current	Coil Rated Voltage		
M 15				M	A	H	001	8	12VDC		
M = 3.5 mm E = 3.2 mm B = 5 mm F = 2.5 mm				A = AgCdO B = AgNi C = AgCdO, Au plated > 3.5 micron D = AgCdO, Au gilded > 0.5 micron E = AgNi, Au plated > 3.5 micron F = AgNi, Au gilded > 0.5 micron S = AgSnO₂				H = Sealed	001 = 1 Change-over 100 = 1 Make contact	8 = 8A	3V - 5V - 6V - 8V - 12V - 24V - 48V - 110V DC

Ordering Key		Contact Material	Rated Coil Voltage	DC/AC	Options
M 25		A	001	024	16
A = AgCdO (Standard) S = AgSnO₂ C = AgNi10, Au plated > 3.5 micron G = AgNi10					
001 = 1 Change-over contact 100 = 1 Make contact 002 = 2 Change-over contacts 200 = 2 Make contacts					
5VDC=005 / 6VDC=006 / 12VDC=012 24VDC=024 / 48VDC=048 / 60VDC=060 110VDC=110					
				16 = 16A (001 - 100) Pin layout 5 mm 12 = 12A (001 - 100) Pin layout 3.5 mm 8 = 8A (002 - 200) Pin layout 5 mm	

Ordering Key		Terminal Version	Contact Code	Rated Coil Voltage	DC/AC
RMI		A	4 5	230	AC
A = Soldering Terminals B = PCB Terminals		2 10 = 2 Change-Over contacts 10A 4 5 = 4 Change-Over contacts 5A		5V-6V-12V-24V-48V-60V-110V DC 6V-12V-24V-48V-115/120V-230V AC	DC = Direct Current Coils AC = Alternate Current Coils



Ordering Key		Number of Pins	Contact Code	Rated Coil Voltage	DC/AC
RCP		11	003	230	AC
8 = Eight Pins 11 = Eleven Pins					
002 = 2 Change-Over Contacts 10A 003 = 3 Change-Over Contacts 10A					
6V-12V-24V-48V-60V-100V-110V DC 6V-12V-24V-48V-115/120V-230V AC					
		DC = Direct Current Coils AC = Alternate Current Coils			

Monostable Midi Industrial and Industrial Relays





- High switching power
- Small size
- Monostable version
- Switching capacity 2 poles version
10 A / 250 VAC - 12 A (5x10⁴ cycles)
- Switching capacity 4 poles version
5 A / 250 VAC - 6 A (5x10⁴ cycles)
- DC coils 5 to 110 VDC
- AC coils 6 to 230 VAC
- 2 or 4 change over contacts
- Standard with LED, locking push to test button and mechanical flag indicator
- 3,750 VAC dielectric coil to contacts
- Sealed according to IP 40 standard
- Conform to the CE low voltage directive

Type **RMI**



- 8 or 11 pin socket mounting
- Monostable version
- Long life (minimum 100,000 electrical operations at 10 A 250 VAC / 30 VDC)
- Switching capacity:
10 A / 250 VAC - 12 A (5x10⁴ cycles)
- DC coils 6 to 110 VDC
- AC coils 6 to 230 VAC
- 2 or 3 change over contacts
- Matched sockets available
- Standard with LED, locking push to test button and mechanical flag indicator
- 3,750 VAC dielectric coil to contacts
- Sealed according to IP 40 standard
- Conform to the CE low voltage directive

Type **RCP**



The Complete Product Package



Sense

Inductive Proximity • Capacitive Proximity
Photoelectric • Ultrasonic • Level Controls
Limit Switches • Magnetic Switches



Control

Timers • Counters • PLCs • Panel Meters
HMI's • PID Controllers • Energy Management
Current & Voltage Monitors • Enclosures and Cabinets



Solid State Relays • Electromechanical Relays
Motor Controllers • Pushbuttons • Switches
Pilot Devices • Cam Switches • Rotary Disconnects



Cable Pull Switches • Interlock Switches • Hinge Switches
And Coming Soon: Electrical Transient Protection
Safety Modules • Mat Systems • Light Curtains

Switch

Safety

A Global Force in Industrial Automation

CARLO GAVAZZI has a multitude of sales offices spanning North America (*not to mention our hundreds of distributors*). Therefore, we can be viewed as "your local automation resource" - assisting you every step of the way in finding the proper solution for your various application requirements. Naturally, our job is greatly simplified as we have such a vast range of solutions to offer you via our comprehensive product package.

Our worldwide sales offices make us an ideal business partner, *especially for manufacturers of exported machinery*, as our products are available locally and they are CE marked.

USA

CARLO GAVAZZI INC.
750 Hastings Lane
Buffalo Grove, IL 60089
Tel 1.847.465.6100
Fax 1.847.465.7373
www.GavazziOnline.com

CANADA

CARLO GAVAZZI (CANADA) INC
2660 Meadowvale Boulevard
Mississauga, Ontario L5N 6M6
Tel 1.905.542.0979, Fax 1.905.542.2248
CARLO GAVAZZI (CANADA) LTÉE
3777 Boulevard du Tricentenaire
Montréal, Quebec H1B 5W3
Tel 1.514.644.2544, Fax 1.514.644.2808
www.GavazziOnline.com

Argentina • Australia • Austria • Bahrain • Belgium • Bolivia • Bosnia • Brazil • Brunei • Bulgaria • Canada
Chile • China • Columbia • Croatia • Cyprus • Czech • Denmark • Dominican Republic • Egypt • Estonia
Finland • France • Germany • Greece • Hungary • Iceland • India • Indonesia • Iran • Ireland • Italy • Japan
Jordan • Kenya • Korea • Kuwait • Lebanon • Malaysia • Malta • Maroc • Mauritius • Mexico • Netherlands
New Zealand • Norway • Pakistan • Papua New Guinea • Paraguay • Peru • Philippines • Poland
Portugal • Qatar • Romania • Russia • Saudi Arabia • Serbia • Singapore • Slovakia • Slovenia • South Africa
Spain • Sultanate of Oman • Sweden • Switzerland • Syria • Taiwan • Thailand • Tunisia • Turkey
Ukraine • United Arab Emirates • United Kingdom • Uruguay • United States of America • Venezuela • Vietnam