

REV	ECN	APPD
—	4800	



RATINGS

CURRENT — 12A
VOLTAGE — 150V
U.L. FILE NO.





RATINGS

CURRENT — 12A
VOLTAGE — 150V
CSA FILE NO.

DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT — 12A
VOLTAGE — 130V
TUV FILE NO.




INSTALLATION RECOMMENDATIONS

WIRE RANGE: 14-30 AWG
WIRE STRIP LENGTH: .200-.240
TIGHTENING TORQUE: 2.2 LB-IN.

MATERIALS

HOUSING: POLYAMIDE 6/6, COLOR: BLACK
CONTACT: COPPER ALLOY, TIN PLATED
SCREW / CAGE CLAMP: COPPER ALLOY, NICKEL PLATED

OPERATING TEMPERATURE RANGE: -40°C TO 110°C
RECOMMENDED PCB THICKNESS: .094 MAX




DIMENSIONS

ANSI Y14.5M
UNITS: INCHES
ACAD FILE

TOLERANCES

.XX ± .01
.XXX ± .005
ANGLES ± 2°

PROJECTION



SPECIFICATION DRAWING

ENGR
I. QUINN 3/20/02

CHKD

APPD



TITLE

ESRM TERMINAL BLOCK
22 POSITION VERTICAL
.150 [3.81mm] PITCH

ORIGINAL
STAMPED
IN RED

THIS DOCUMENT CONTAINS
PROPRIETARY INFORMATION WHICH
IS THE CONFIDENTIAL PROPERTY
OF PCD, INC. PEABODY, MA, USA

SIZE

A

DWG NO.

ESRM22290

REV

—

CODE: 58982

SCALE: NONE

SHEET 1 OF 1