

TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

TC7MBL3125CFT, TC7MBL3125CFK
TC7MBL3126CFT, TC7MBL3126CFK**Low Voltage/Low Capacitance Quad Bus Switch**

The TC7MBL3125C and TC7MBL3126C are a Low Voltage/Low Capacitance CMOS 4bit Bus Switch. The low on-resistance of the switch allows connections to be made with minimal propagation delay time.


The TC7MBL3125C requires the output enable (\overline{OE}) input to be set high to place the output into the high impedance state, whereas the TC7MBL3126C requires the output enable (OE) input to be set low to place the output into the high impedance.

All inputs are equipped with protection circuits against static discharge.

Features


- Operating voltage : $V_{CC} = 1.65$ to 3.6 V
- On-capacitance : $C_{I/O} = 7.5$ pF Switch On (typ.) @ $V_{CC} = 3$ V
- On-resistance : $RON = 6.5 \Omega$ (typ.) @ $V_{CC} = 3$ V, $V_{I/O} = 0$ V
- ESD performance : Machine model $\geq \pm 200$ V
Human body model $\geq \pm 2000$ V
- Power-down protection for inputs (\overline{OE} , OE and I/O)
- Package: TSSOP14,VSSOP14 (US14),

TC7MBL3125CFT, TC7MBL3126CFT



TSSOP14-P-0044-0.65A

TC7MBL3125CFK, TC7MBL3126CFK



VSSOP14-P-0030-0.50

Weight


| | |
|----------------------|-----------------|
| TSSOP14-P-0044-0.65A | : 0.06 g (typ.) |
| VSSOP14-P-0030-0.50 | : 0.02 g (typ.) |

Start of commercial production
2008-06

Pin Assignment (top view)


TC7MBL3125C

FT (TSSOP14-P-0044-0.65A)
FK (VSSOP14-P-0030-0.50)



TC7MBL3126C

FT (TSSOP14-P-0044-0.65A)
FK (VSSOP14-P-0030-0.50)




Truth Table


| Inputs (3125) | Inputs (3126) | Function |
|-----------------|---------------|-----------------|
| \overline{OE} | OE | |
| L | H | A port = B port |
| H | L | Disconnect |

System Diagram

TC7MBL3125C



TC7MBL3126C



Absolute Maximum Ratings (Note)

| Characteristic | Symbol | Rating | Unit |
|---------------------------------|-----------------------------------|------------------------------|------|
| Power supply range | V _{CC} | -0.5 to 4.6 | V |
| Control pin input voltage | V _{IN} | -0.5 to 4.6 | V |
| Switch terminal I/O voltage | V _S | -0.5 to 4.6 | V |
| | V _S | -0.5 to V _{CC} +0.5 | |
| Clamp diode current | I _{IK} | -50 | mA |
| Switch I/O current | I _S | 50 | mA |
| Power dissipation | P _D | 180 | mW |
| DC V _{CC} /GND current | I _{CC} /I _{GND} | ±100 | mA |
| Storage temperature | T _{STG} | -65 to 150 | °C |

Note: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant change in temperature, etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings and the operating ranges.

Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

Operating Ranges (Note)

| Characteristic | Symbol | Rating | Unit |
|-----------------------------|------------------|----------------------|------|
| Power supply voltage | V _{CC} | 1.65 to 3.6 | V |
| Control pin input voltage | V _{IN} | 0 to 3.6 | V |
| Switch terminal I/O voltage | V _S | 0 to 3.6 | V |
| | V _S | 0 to V _{CC} | |
| Operating temperature | T _{OPR} | -40 to 85 | °C |
| Input rise and fall time | dt/dv | 0 to 10 | ns/V |

Note: The operating ranges must be maintained to ensure the normal operation of the device.

Unused inputs must be tied to either V_{CC} or GND.

Electrical Characteristics

DC Characteristics (Ta = -40 to 85°C)

| Characteristics | | Symbol | Test Condition | V _{CC} (V) | Min | Typ. | Max | Unit |
|---|-----------|------------------|--|---------------------|-----------------------|------|-----------------------|------|
| Input voltage OE, OE | “H” level | | — | 1.65 to 3.6 | 0.7 × V _{CC} | — | — | V |
| | “L” level | V _{IL} | — | 1.65 to 3.6 | — | — | 0.3 × V _{CC} | |
| Input leakage current OE, OE | | I _{IN} | V _{IN} = 0 to 3.6 V | 1.65 to 3.6 | — | — | ±1.0 | μA |
| Power-off leakage current | | I _{OFF} | OE, OE, A, B = 0 to 3.6 V | 0 | — | — | 10 | μA |
| Off-state leakage current (switch off) | | I _{SZ} | A, B = 0 V to V _{CC} , OE = V _{CC} (3125), OE=GND(3126) | 1.65 to 3.6 | — | — | ±1.0 | μA |
| On resistance (Note 1) (Note 2) | | R _{ON} | V _{IS} = 0 V, I _{IS} = 30 mA | 3.0 | — | 6.5 | 11 | Ω |
| | | | V _{IS} = 3.0 V, I _{IS} = 30 mA | 3.0 | — | 11 | 17 | |
| | | | V _{IS} = 2.4 V, I _{IS} = 15 mA | 3.0 | — | 13 | 19 | |
| | | | V _{IS} = 0 V, I _{IS} = 24 mA | 2.3 | — | 7 | 11 | |
| | | | V _{IS} = 2.3 V, I _{IS} = 24 mA | 2.3 | — | 14 | 21 | |
| | | | V _{IS} = 2.0 V, I _{IS} = 15 mA | 2.3 | — | 16 | 23 | |
| | | | V _{IS} = 0 V, I _{IS} = 4 mA | 1.65 | — | 8 | 14 | |
| | | | V _{IS} = 1.65 V, I _{IS} = 4 mA | 1.65 | — | 19 | 27 | |
| Quiescent supply current | | I _{CC} | V _{IN} = V _{CC} or GND, I _{OUT} = 0 A | 3.6 | — | — | 10 | μA |

Note1: All typical values are at Ta = 25°C.

Note2: Measured by the voltage drop between A and B pins at the indicated current through the switch.
On resistance is determined by the lower of the voltages on the two (A or B) pins.


AC Characteristics (Ta = -40 to 85°C)

| Characteristics | Symbol | Test Condition | VCC (V) | Min | Max | Unit |
|---------------------|------------------------|--------------------|------------|-----|-----|------|
| | | | | | | |
| Output enable time | t_{pZL} t_{pZH} | Figure 1, Figure 2 | 3.3 ± 0.3 | — | 6 | ns |
| | | | 2.5 ± 0.2 | — | 7 | |
| | | | 1.8 ± 0.15 | — | 11 | |
| Output disable time | t_{pLZ} t_{pHZ} | Figure 1, Figure 2 | 3.3 ± 0.3 | — | 6 | ns |
| | | | 2.5 ± 0.2 | — | 7 | |
| | | | 1.8 ± 0.15 | — | 11 | |

Capacitive Characteristics (Note) (Ta = 25°C)

| Characteristics | Symbol | Test Condition | VCC (V) | Typ. | Unit |
|--|-----------|--|---------|------|------|
| | | | | | |
| Control pin input capacitance | C_{IN} | $V_{IN} = 0 \text{ V}$ | 3.0 | 4 | pF |
| Switch terminal capacitance (Switch Off) | $C_{I/O}$ | $\overline{OE} = V_{CC}$, $OE = GND$, $V_{IS} = 0 \text{ V}$ | 3.0 | 3.5 | pF |
| Switch terminal capacitance (Switch On) | $C_{I/O}$ | $\overline{OE} = GND$, $OE = V_{CC}$, $V_{IS} = 0 \text{ V}$ | 3.0 | 7.5 | pF |

Note: This parameter is guaranteed by design

RON - V_{IS} Characteristic (typ.) Ta = 25°C

AC Test Circuit





Figure 1 AC Test Circuit

AC Waveform

Figure 2 t_{pLZ} , t_{pHZ} , t_{pZL} , t_{pZH}

Rise and Fall Times (tr / tf) of the TC7MBL3125C, 3126C I/O Signals

The tr(out) and tf(out) values of the output signals are affected by the CR time constant of the input, which consists of the switch terminal capacitance (Cl/O) and the on-resistance (RON) of the input.

In practice, the tr(out) and tf(out) values are also affected by the circuit's capacitance and resistance components other than those of the TC7MBL3125C, 3126C.

The tr(out) / tf(out) values can be approximated as follows. (Figure 3 shows the test circuit.)

$$tr(out) / tf(out) (\text{approx}) = - (Cl/O + CL) \cdot (RDRIVE + RON) \cdot \ln (((V_{OH} - V_{OL}) - V_M) / (V_{OH} - V_{OL}))$$

where RDRIVE is the output impedance of the previous-stage circuit.

Calculation example:

$$tr(out) (\text{approx}) = - (7.5 + 15) \cdot 10^{-12} \cdot (120 + 6.5) \cdot \ln (((3.0 - 0) - 1.5) / (3.0 - 0)) \\ \approx 2.0 \text{ ns}$$

Calculation conditions:

VCC = 3.0 V, CL = 15 pF, RDRIVE = 120 Ω (output impedance of the previous IC), VM = 1.5 V (VCC / 2)

Output of the previous IC = digital (i.e., high-level voltage = VCC; low-level voltage = GND)





Figure 3 Test Circuit

Package Dimensions

TSSOP14-P-0044-0.65A

Unit: mm




Weight: 0.06 g (typ.)

Package Dimensions

VSSOP14-P-0030-0.50

Unit: mm



Weight: 0.02 g (typ.)

RESTRICTIONS ON PRODUCT USE

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. **TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.**
- **PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT ("UNINTENDED USE").** Except for specific applications as expressly stated in this document, Unintended Use includes, without limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions, safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. **IF YOU USE PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT.** For details, please contact your TOSHIBA sales representative.
- Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- **ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.**
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile technology products (mass destruction weapons). Product and related software and technology may be controlled under the applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. **TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.**