

PC1004A-L (10x4) Character LCD Display

Features	Absolute Maximum Ratings at T _A = 25 °C				
	Item	Symbol	Min	Max	Unit
	Power Supply (Logic)	Vdd	-0.3	7.0	V
	Power Supply (LCD)	Vo	Vdd - 0.3	Vdd 12.0	V
	Input Voltage	Vi	- 0.3	Vdd	V
	Operating Temperature (Standard)	Topr	0	50	°C
	Storage Temperature (Standard)	Tstg	- 20	70	°C
	Extended Operating Temperature	Topr	- 20	70	°C
	Extended Storage Temperature	Tstg	- 30	80	°C

*10 Character, 4 Line
*View Angle 12H or 6H
*TN or STN Fluid
*Extended Temperature Range available
*Several Character Types available
*LED or EL Backlight available

Electrical Characteristics at T_A = 25 °C, Vdd=5V+0.25V

Item	Symbol	Min	Typ	Max	Unit
Power Supply (Logic)	Vdd-Vss	4.7	5.0	5.3	V
Supply Current	Idd	—	2.0	4.0	mA
LCD Driving Voltage	Vdd - Vo	4.2	4.5	4.8	V
Input Voltage “H”	Vih	2.2	—	Vdd	V
Input Voltage “L”	Vil	—	—	0.6	V
Output Voltage “H”	Voh	2.4	—	—	V
Output Voltage “L”	Vol	—	—	0.4	V

Interface Pin Connection

No	Symbol	Function	No	Symbol	Function
1	Vss	Power Supply (GND)	9	DB2	Data Bus Line 2
2	Vdd	Power Supply (+5V)	10	DB3	Data Bus Line 3
3	Vo	Contrast Adjust	11	DB4	Data Bus Line 4
4	RS	Instruction/Register Select	12	DB5	Data Bus Line 5
5	R/W	Read/Write	13	DB6	Data Bus Line 6
6	E	Enable Signal	14	DB7	Data Bus Line 7
7	DB0	Data Bus Line 0	15	A	Power Supply for LED Backlight (+)
8	DB1	Data Bus Line 1	16	K	Power Supply for LED Backlight (-)

LED Backlight Specifications


Forward Voltage	Forward Current	Power Dissipation	Peak Wavelength
4.2V (Typ)	(Max)	(Max)	570nm (Typ)

Mechanical Specifications


Item	Overall Size	Viewing Area	Character Size	Character Pitch	Dot Size
Specifications	57.0W x 57.0H x 8.8T (BL12.7T)	39.0W x 24.40H	2.95W x 4.75H	3.55W x 5.35H	0.55W x 0.55H

All dimensions are in mm. Tolerance is ± 0.3 Unless otherwise specified


PC1004A-L (10x4) Character LCD Display



Block Diagram



Character Dot Layout



All dimensions are in mm. Tolerance is ± 0.3 Unless otherwise specified