


-1	LEADMAKER	AIRFEED	
-2	BENCH MODEL K	AIRFEED	
-3	BENCH MODEL G	AIRFEED	



- | | | | | | | | |
|--|--|-------------------------------|--|------------------|--|---|--|
| QTY REQD PER ASSY | | | | PARTS LIST | | | |
| DIMENSIONS IN INCHES.
DO NOT SCALE PRINT. | | MATL | | HT TR | | FIN | |
| TOLERANCES UNLESS
SPECIFIED: | | - | | - | | - | |
| 2 PLC DEC ± .25 | | DR 20FEB02 | | APP 22FEB02 | |  AMP Incorporated
Harrisburg, PA 17105-3608 | |
| 3 PLC DEC ± | | R.O.WILSON | | T.ELBIN | | | |
| 4 PLC DEC ± | | CHK 21FEB02 | | REL - | | | |
| ANGLES ± | | R.O.WILSON | | - | | | |
| SURF TEXTURE: ✓ | | NAME SIDE FEED HDM APPLICATOR | | | | MACHINE REF | |
| REMOVE BURRS, BREAK
SHARP EDGES R.015 MAX | | SCALE - | | D DWG NO 1385384 | | MINI APPL | |
| CASE CODE 00779 | | CUSTOMER AND ASSEMBLY DRAWING | | | | SHEET 1 OF 1 REV A | |
| | | | | | | RESTRICTED TO - | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385384-3](#)