


NUMBER 201589

USED ON

- 201589 -1** 1. AS SHOWN.
- OBSOLETE 201589 -2** 1. SAME AS -1 EXCEPT:
2. FINISH OF ITEM 1, .0001 MIN SILVER OVER .00005 MIN NI
- OBSOLETE 201589 -3** 1. SAME AS -1 EXCEPT:
2. FINISH OF ITEM 1, .0001 MIN GOLD OVER .0001 MIN SILVER
- OBSOLETE 201589 -4** 1. SAME AS -1 EXCEPT:
2. MTD ON TAPE.



ITEM 1
SOCKET BODY
COPPER ALLOY
.00003 MIN GOLD OVER .00005 MIN NICKEL

WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:

- 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
- 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER—
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL

© 1961 BY AMP INC. HARRISBURG, PENNA.
AMP AND ITS LOGO ARE REGISTERED TRADEMARKS OF AMP INC.

PRINT DIST 394
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.
PROPOSAL NO C/PW-461-X13

M	OBS-24-3 ECN BD3038	2.8.10.87
L	REV PER ECN BD2619	THW 3.89
K	OBSOLETE -4 PER	34350 THW 12-87
J	REVISED	3442 THW 9-87
H	INACTIVATED -4	J 003 2/22/86
G	REV. PER ECN	B 838 2/22/86
F	NOTE ADDED	B 141 2/22/86
E	REV RETAINER SPRING TO SST	Z 208 2/22/86
D	AGE -4	Z 361 2/22/86
C	REVISED	W-525 2/22/86
B	REVISED	W-525 2/22/86
A	REVISED	W-525 2/22/86
LTR	REVISION RECORD	ECA BY DATE

REF: 1950-317-35

TO
EXCEPT AS NOTED
DECIMALS = 005
FRACTIONS = 1/16

MATERIAL SEE CALL OUT	DR J. R. Ruff 11/16/61	ENGR J. R. Ruff 11-16-61
HEAT TREAT H	CHK J. R. Ruff 11-30-61	APP J. R. Ruff 11/16/61
AMP AMP INCORPORATED HARRISBURG, PENNA.		
NAME #20 SOCKET CONTACT ASSY		
WIRE SIZE 18-16		
SCALE 10:1	LOC BD	NO 201589
REV M		

CUSTOMER DRAWING