



NOTES:

1. Rating: 300V 30A (UL)
2. Insulation Withstanding Voltage: AC2000V/MIN
3. Insulation Resistance: $\geq 500M\Omega$ or more at DC500V
4. Temperature Range: $-33^{\circ}C/+105^{\circ}C$
5. Screw Torque Value: 7.0 lbf-in (UL)
6. Suitable Electric Wire: 10-20AWG

RoHS Compliant

DTM	P	2	3	4	5	6	7	8	9	10	11	12
L		19.5	31.5	43.5	55.5	67.5	79.5	91.5	103.5	115.5	127.5	139.5
TOL (±)		0.08	0.12	0.16	0.20	0.24	0.28	0.32	0.36	0.40	0.44	0.48

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE	ES1200 Series - 12.0mm Euro Strip, Wire guard, flat base											
PART NO.	ES1200/XXDSFB (XX - number of poles per row)				DWG NO.	ES1200/XXDSFB.DWG						
APPROVED	CHECKED	DESIGNED	DRAWN		5020			Tolerance				
KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01	KSZ 2007.08.01					UNIT: mm	X	±015		
					SHEET: 01/01			SCALE: NONE	.XX	±0.075		
								REV.: A	.XXX	±0.05		