



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P2	REVISED PER ECR-16-014469	17OCT2016	BW	RS

D




1. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.
2. WIRE RANGE: 0.5-0.15 mm²(30-26 AWG)
3. 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [.000050] MIN NICKEL.


C



B




SECTION B-B
SCALE 20:1



SECTION A-A
SCALE 20:1

3	0.20 [.008] PH BRZ	1-770834-1
3	0.20 [.008] BRASS	1-770834-0
1	0.20 [.008] PH BRZ	770834-6
PRE-TIN	0.20 [.008] PH BRZ	770834-4
1	0.20 [.008] BRASS	770834-3
PRE-TIN	0.20 [.008] BRASS	770834-1
FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	S. HOOVER	17OCT02	 TE Connectivity					
			CHK	C. JONES	17OCT02						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	C. JONES	17OCT02	NAME SOCKET, MINI UNIVERSAL MATE-N-LOK(TM)				
		0 PLC ± -		PRODUCT SPEC		APPLICATION SPEC					
		1 PLC ± -		—							
		2 PLC ± -		—							
		3 PLC ± 0.15[.006]		—							
		4 PLC ± -		—							
ANGLES		± 1°		—		RESTRICTED TO					
MATERIAL		FINISH		WEIGHT		A2 00779		DRAWING NO		G-770834	
-		-		0.000000		A2 00779		G-770834		-	
CUSTOMER DRAWING						SCALE		10:1		SHEET 1 of 1	
										REV P2	